


**DFFC 0.2-0.35 ZRV1.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

Similar to illustration

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Crimp contact (terminal), 0.35 mm <sup>2</sup>
Order No.	<a href="#">1705310000</a>
Type	DFFC 0.2-0.35 ZRV1.5
GTIN (EAN)	4008 190948573
Qty.	500 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-12-31T00:00:00+01:00

**DFFC 0.2-0.35 ZRV1.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 0.21 g

**Temperatures**

Ambient temperature -5 °C...40 °C      Operating temperature 130 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Material data**

Basic material Plastic      Surface finish tinned  
 Colour silver

**System specifications**

Version for holding 0.2 ... 0.35 mm<sup>2</sup>

**Additional technical data**

Installation advice Direct mounting

**Conductors for clamping (rated connection)**

Stripping length 6 mm      Type of connection Crimp contact  
 Wire connection cross-section, finely 0.35 mm<sup>2</sup>  
 stranded with wire-end ferrules DIN 46228/1, max. Wire connection cross section, finely 0.35 mm<sup>2</sup>  
 stranded, max.

**General**

Installation advice Direct mounting      Surface finish tinned

**Rating data**

Rated cross-section 0.35 mm<sup>2</sup>      Volume resistance according to IEC 1.83 mΩ  
 60947-7-x  
 Power loss in accordance with IEC 0.56 W  
 60947-7-x

**Classifications**

ETIM 8.0 EC000796      ETIM 9.0 EC000796  
 ETIM 10.0 EC000796      ECLASS 14.0 27-44-02-04  
 ECLASS 15.0 27-44-02-04