

**DFFC 0.2-0.35 ZRV1.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

## Similar to illustration

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

|            |  |
|------------|--|
| Version    | Crimp contact (terminal), 0.35 mm <sup>2</sup> |
| Order No.  | <a href="#">1705310000</a>                     |
| Type       | DFFC 0.2-0.35 ZRV1.5                           |
| GTIN (EAN) | 4008190948573                                  |
| Qty.       | 500 items                                      |

## DFFC 0.2-0.35 ZRV1.5

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

|      |         |
|------|---------|
| RoHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 0.21 g |
|------------|--------|

## Temperatures

|                     |               |                       |        |
|---------------------|---------------|-----------------------|--------|
| Ambient temperature | -5 °C...40 °C | Operating temperature | 130 °C |
|---------------------|---------------|-----------------------|--------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                |         |                |        |
|----------------|---------|----------------|--------|
| Basic material | Plastic | Surface finish | tinned |
| Colour         | silver  |                |        |

## System specifications

|         |  |
|---------|--|
| Version | for holding 0.2 ... 0.35 mm <sup>2</sup> |
|---------|--|

## Additional technical data

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

## Conductors for clamping (rated connection)

|   |                      |  |                      |
|---|----------------------|--|----------------------|
| Stripping length  | 6 mm                 | Type of connection                                   | Crimp contact        |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 0.35 mm <sup>2</sup> | Wire connection cross section, finely stranded, max. | 0.35 mm <sup>2</sup> |

## General

|                     |                 |                |        |
|---------------------|-----------------|----------------|--------|
| Installation advice | Direct mounting | Surface finish | tinned |
|---------------------|-----------------|----------------|--------|

## Rating data

|   |                      |  |         |
|---|----------------------|--|---------|
| Rated cross-section                         | 0.35 mm <sup>2</sup> | Volume resistance according to IEC 60947-7-x | 1.83 mΩ |
| Power loss in accordance with IEC 60947-7-x | 0.56 W               |  |         |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000796    | ETIM 9.0    | EC000796    |
| ETIM 10.0   | EC000796    | ECLASS 14.0 | 27-44-02-04 |
| ECLASS 15.0 | 27-44-02-04 |             |             |