


**SERV-P. DIAM16 L2 SW/WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

Service Pack is a bag with pre-printed symbols on perforated sheets. The all-round solution for labelling electrical systems is highly resistant to alkyl alcohols and benzenes.

**General ordering data**

|            |                                                   |
|------------|---------------------------------------------------|
| Version    | Device markers, Device markers, 16 x 16 mm, black |
| Order No.  | <a href="#">1707350002</a>                        |
| Type       | SERV-P. DIAM16 L2 SW/WS                           |
| GTIN (EAN) | 4008190925321                                     |
| Qty.       | 1 items                                           |

**SERV-P. DIAM16 L2 SW/WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.08 mm | Depth (inches)  | 0.0031 inch |
| Height     | 16 mm   | Height (inches) | 0.6299 inch |
| Width      | 16 mm   | Width (inches)  | 0.6299 inch |
| Net weight | 34.32 g |                 |             |

**Temperatures**

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -45...80 °C |
|-----------------------------|-------------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**General data**

|                                              |                                           |             |
|----------------------------------------------|-------------------------------------------|-------------|
| Adhesive                                     | Permanent acrylic copolymer               |             |
| Material colour according to resistance code | 0                                         |             |
| Number per sheet                             | 20                                        |             |
| Version                                      | Self-adhesive                             |             |
| Width                                        | 16 mm                                     |             |
| Operating temperature range, max.            | 80 °C                                     |             |
| Operating temperature range, min.            | -45 °C                                    |             |
| Colour                                       | black                                     |             |
| Basic material                               | Acrylic-coated fibre webbing              |             |
| Printed characters                           | Mixed characters                          |             |
| Number of markers per packaging unit         | 200                                       |             |
| Number of markers per packaging unit         | Form of supply                            | Label sheet |
|                                              | Number of combinations per packaging unit | 10          |
|                                              | Number of markers per combination         | 20          |
| Number of markers per combination            | 1 Label sheet = 20 Device markers         |             |
| Operating temperature range                  | -45...80 °C                               |             |
| Imprint                                      | L2                                        |             |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |