


BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Female plugs with crimp wire connection system. The female plugs provide space for labelling and can be coded.

General ordering data

| | |
|--------------|---|
| Version | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 8, 180°, Crimp connection, Clamping range, max. : 2.5 mm ² , Box |
| Order No. | 1712020000 |
| Type | BLC 5.08/08/180R BK BX |
| GTIN (EAN) | 4008190935030 |
| Qty. | 50 items |
| Product data | IEC: 400 V / 21 A UL: 300 V / 10 A / AWG 26 - AWG 14 |
| Packaging | Box |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E60693 |

Dimensions and weights

| | |
|------------|----------|
| Depth | 24.5 mm |
| Height | 10.1 mm |
| Width | 40.64 mm |
| Net weight | 4.59 g |

| | |
|-----------------|-------------|
| Depth (inches) | 0.9646 inch |
| Height (inches) | 0.3976 inch |
| Width (inches) | 1.6 inch |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

System Parameters

| | |
|--|-------------------------------------|
| Product family | OMNIMATE Signal - series BL/SL 5.08 |
| Wire connection method | Crimp connection |
| Pitch in inches (P) | 0.200 " |
| Number of poles | 8 |
| L1 in inches | 1.400 " |
| Pin series quantity | 1 |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch |
| Protection degree | IP20 |
| Can be coded | Yes |
| Plugging cycles | 25 |
| Pulling force/pole, max. | 6.5 N |

| | |
|--|------------------------------|
| Type of connection | Field connection |
| Pitch in mm (P) | 5.08 mm |
| Conductor outlet direction | 180° |
| L1 in mm | 35.56 mm |
| Number of rows | 1 |
| Rated cross-section | 2.5 mm ² |
| Touch-safe protection acc. to DIN VDE 0470 | IP20 plugged/ IP10 unplugged |
| Volume resistance | ≤5 mΩ |
| Stripping length | 5 mm |
| Plugging force/pole, max. | 8.5 N |

Material data

| | |
|---------------------------------------|----------------------------|
| Insulating material | PBT GF |
| Colour chart (similar) | RAL 9011 |
| Comparative Tracking Index (CTI) | ≥ 200 |
| UL 94 flammability rating | V-0 |
| Layer structure of plug contact | 4...8 µm Sn hot-dip tinned |
| Storage temperature, max. | 70 °C |
| Operating temperature, max. | 100 °C |
| Temperature range, installation, max. | 100 °C |

| | |
|---------------------------------------|----------|
| Colour | black |
| Insulating material group | IIIa |
| Moisture Level (MSL) | |
| Contact material | Cu-alloy |
| Storage temperature, min. | -40 °C |
| Operating temperature, min. | -50 °C |
| Temperature range, installation, min. | -25 °C |

Conductors suitable for connection

| | |
|---|--|
| Clamping range, min. | 0.22 mm ² |
| Wire connection cross section AWG, min. | AWG 24 |
| Flexible, min. H05(07) V-K | 0.5 mm ² |
| Reference text | The outside diameter of the plastic collar should not be larger than the pitch |

| | |
|---|---------------------|
| Clamping range, max. | 2.5 mm ² |
| Wire connection cross section AWG, max. | AWG 14 |
| Flexible, max. H05(07) V-K | 2.5 mm ² |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

(P), Length of ferrules is to be chosen depending on the product and the rated voltage.

Rated data acc. to IEC

| | | | |
|---|------------------------|---|-------------------|
| tested acc. to standard | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C) | 21 A |
| Rated current, max. number of poles (Tu=20°C) | 14.5 A | Rated current, min. number of poles (Tu=40°C) | 18 A |
| Rated current, max. number of poles (Tu=40°C) | 12.5 A | Rated voltage for surge voltage class / pollution degree II/2 | 400 V |
| Rated voltage for surge voltage class / pollution degree III/2 | 320 V | Rated voltage for surge voltage class / pollution degree III/3 | 250 V |
| Rated impulse voltage for surge voltage class/ pollution degree II/2 | 4 kV | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV | Short-time withstand current resistance | 3 x 1s with 120 A |

Rated data acc. to CSA

| | | | |
|-----------------------------------|--|-----------------------------------|-----------|
| Institute (CSA) | CSA | Certificate No. (CSA) | 12400-374 |
| Rated voltage (Use group B / CSA) | 300 V | Rated voltage (Use group D / CSA) | 300 V |
| Rated current (Use group B / CSA) | 10 A | Rated current (Use group D / CSA) | 10 A |
| Wire cross-section, AWG, min. | AWG 26 | Wire cross-section, AWG, max. | AWG 14 |
| Reference to approval values | Specifications are maximum values, details - see approval certificate. | | |

Rated data acc. to UL 1059

| | | | |
|---------------------------------------|--|---------------------------------------|--------|
| Institute (UR) | UR | Certificate No. (UR) | E60693 |
| Rated voltage (Use group B / UL 1059) | 300 V | Rated voltage (Use group D / UL 1059) | 300 V |
| Rated current (Use group B / UL 1059) | 10 A | Rated current (Use group D / UL 1059) | 10 A |
| Wire cross-section, AWG, min. | AWG 26 | Wire cross-section, AWG, max. | AWG 14 |
| Reference to approval values | Specifications are maximum values, details - see approval certificate. | | |

Packing

| | | | |
|-----------|-----------|------------|-----------|
| Packaging | Box | VPE length | 145.00 mm |
| VPE width | 115.00 mm | VPE height | 66.00 mm |

Type tests

| | | |
|------------------------------|------------|--|
| Test: Durability of markings | Standard | draft DIN VDE 0627 section 6.2.2 / 09.91, DIN IEC 512 part 7 section 5 / 05.94 |
| | Test | durability |
| | Evaluation | passed |

Important note

| | |
|----------------|--|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request. |
| Notes | <ul style="list-style-type: none"> Additional variants on request Rated current related to rated cross-section & min. No. of poles. Rated cross-section depends on crimp contact used. |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

Technical data

www.weidmueller.com

- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months




Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002638 | ETIM 9.0 | EC002638 |
| ETIM 10.0 | EC002638 | ECLASS 14.0 | 27-46-02-02 |
| ECLASS 15.0 | 27-46-02-02 | | |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings**Product image****Dimensional drawing****Graph**

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories



Blocks for PCB mounting

Minor component, major effect:

Clip-on attachment elements increase the mechanical resilience of the whole plug connection by

- securing the male connectors to the circuit board
- providing a vibration-proof connection between the sockets and the male connectors

Clip-on or pre-assembled - always the right solution:

- Hard-wearing, precise fitting dovetail joint
- Hard-wearing metal threaded inserts
- Suitable for all outlet directions

Maximum stability, minimum effort:

- Extremely resilient for frequent fastening operations
- Complete set for easy selection

The result: soldering points, contacts and overall module are more resilient against mechanical stress such as vibrations and tensile loads.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SLA BB12R SW | Version |
| Order No. | 1626880000 | PCB plug-in connector, Accessories, Mounting block, black, Number |
| GTIN (EAN) | 4008190198213 | of poles: 0 |
| Qty. | 100 ST | |
| Type | SLA BB12R OR | Version |
| Order No. | 1593450000 | PCB plug-in connector, Accessories, Mounting block, orange, Number |
| GTIN (EAN) | 4008190122164 | of poles: 0 |
| Qty. | 100 ST | |
| Type | SLA BB11R SW | Version |
| Order No. | 1692340000 | PCB plug-in connector, Accessories, Mounting block, black, Number |
| GTIN (EAN) | 4008190864965 | of poles: 0 |
| Qty. | 20 ST | |
| Type | SLA BB11R OR | Version |
| Order No. | 1604120000 | PCB plug-in connector, Accessories, Mounting block, orange, Number |
| GTIN (EAN) | 4008190182977 | of poles: 0 |
| Qty. | 20 ST | |

Coding elements



Only connects what is supposed to be connected: the right connection at the right place.

Coding elements and locking devices clearly assign connecting elements during the manufacturing process and operation

The coding elements and locking devices are inserted prior to assembly or during the cable assembly phase. The Weidmüller alternative: configure online using the variant configurator to precode prior to delivery.

Incorrect assembly on the circuit board and incorrect plugging of connecting elements is no longer possible. The advantage: no troubleshooting during manufacture and no operational errors by the user.

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories**General ordering data**

| | | |
|------------|----------------------------|--|
| Type | BLZ/SL KO BK BX | Version |
| Order No. | 1545710000 | PCB plug-in connector, Accessories, Coding element, black, Number |
| GTIN (EAN) | 4008190087142 | of poles: 1 |
| Qty. | 50 ST | |
| Type | BLZ/SL KO OR BX | Version |
| Order No. | 1573010000 | PCB plug-in connector, Accessories, Coding element, orange, Number |
| GTIN (EAN) | 4008190048396 | of poles: 1 |
| Qty. | 100 ST | |

Crimp contacts**General ordering data**

| | | |
|------------|----------------------------|--|
| Type | DFFC 0.22-0.35 SN 3000 | Version |
| Order No. | 1604230000 | PCB plug-in connector, Crimp contact, Contact, tinned, Max. clamping |
| GTIN (EAN) | 4008190117498 | range : 0.35 mm ² |
| Qty. | 3000 ST | |
| Type | DFFC 0.22-0.35 SN E | Version |
| Order No. | 1604250000 | PCB plug-in connector, Crimp contact, Contact, tinned, Max. clamping |
| GTIN (EAN) | 4008190042905 | range : 0.35 mm ² |
| Qty. | 250 ST | |
| Type | DFFC 0.5-1.0 SN 3000 | Version |
| Order No. | 1480000000 | PCB plug-in connector, Crimp contact, Contact, tinned, Max. clamping |
| GTIN (EAN) | 4008190179175 | range : 1 mm ² |
| Qty. | 3000 ST | |
| Type | DFFC 0.5-1.0 SN E | Version |
| Order No. | 1567060000 | PCB plug-in connector, Crimp contact, Contact, tinned, Max. clamping |
| GTIN (EAN) | 4008190166991 | range : 1 mm ² |
| Qty. | 250 ST | |
| Type | DFFC 1.5-2.5 SN 2500 | Version |
| Order No. | 1480100000 | PCB plug-in connector, Crimp contact, Contact, tinned, Max. clamping |
| GTIN (EAN) | 4008190100414 | range : 2.5 mm ² |
| Qty. | 2500 ST | |
| Type | DFFC 1.5-2.5 SN E | Version |
| Order No. | 1567070000 | PCB plug-in connector, Crimp contact, Contact, tinned, Max. clamping |
| GTIN (EAN) | 4008190059071 | range : 2.5 mm ² |
| Qty. | 250 ST | |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**... for Weidmüller DFF and ZRV contacts**

Crimping tools for for turned/stamped contact
• Ratchet guarantees precise crimping
• Release option in the event of incorrect operation
• With stop for exact positioning of the contacts.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HTF DFF | Version |
| Order No. | 9014140000 | Pressing tool, Crimping tool for contacts, 0.22mm ² , 2.5mm ² , B-Crimp |
| GTIN (EAN) | 4008190297305 | |
| Qty. | 1 ST | |


BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Counterpart

SLDF 5.08



Male connector for through-panel mounting with optional locking function. Internal connection as flat-blade or solder connection. These male connectors provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SLDF 5.08 L/F 8 SN OR BX | Version |
| Order No. | 1599190000 | PCB plug-in connector, male header, 5.08 mm, Number of poles: 8, |
| GTIN (EAN) | 4008190126544 | 180°, Flat-blade connection, Solder connection, Box |
| Qty. | 30 ST | |

SL 5.08/135



Male connectors with 135° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SL 5.08/08/135 3.2SN OR... | Version |
| Order No. | 1603120000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4008190159771 | connection, 5.08 mm, Number of poles: 8, 135°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, orange, Box |

SL 5.08/135B



Male connectors with 135° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SL 5.08/08/135B 3.2SN O... | Version |
| Order No. | 1605590000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4008190027155 | solder connection, 5.08 mm, Number of poles: 8, 135°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, orange, Box |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Counterpart

SL 5.08/180



Male connectors with straight outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SL 5.08/08/180 3.2SN OR... | Version |
| Order No. | 1517860000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4008190170264 | connection, 5.08 mm, Number of poles: 8, 180°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, orange, Box |

SL 5.08/180B



Male connectors with straight outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SL 5.08/08/180B 3.2SN O... | Version |
| Order No. | 1520160000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4008190136741 | solder connection, 5.08 mm, Number of poles: 8, 180°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, orange, Box |

SL 5.08/90



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SL 5.08/08/90 3.2SN OR ... | Version |
| Order No. | 1508660000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4008190178376 | connection, 5.08 mm, Number of poles: 8, 90°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, orange, Box |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Counterpart

SL 5.08/90B




Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The pin headers provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SL 5.08/08/90B 3.2SN OR... | Version |
| Order No. | 1510960000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4008190167295 | solder connection, 5.08 mm, Number of poles: 8, 90°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, orange, Box |

SL 5.08HC/180




Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SL 5.08HC/08/180 3.2SN ... | Version |
| Order No. | 1148250000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4032248933341 | connection, 5.08 mm, Number of poles: 8, 180°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |
| Type | SL 5.08HC/08/180 3.2SN ... | Version |
| Order No. | 1146490000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4032248108855 | connection, 5.08 mm, Number of poles: 8, 180°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, orange, Box |

SL 5.08HC/180B



Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.


BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart**General ordering data**


| | | |
|------------|----------------------------|--|
| Type | SL 5.08HC/08/180B 3.2SN... | Version |
| Order No. | 1149600000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248935000 | solder connection, 5.08 mm, Number of poles: 8, 180°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, black, Box |
| Type | SL 5.08HC/08/180B 3.2SN... | Version |
| Order No. | 1147510000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248934645 | solder connection, 5.08 mm, Number of poles: 8, 180°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, orange, Box |

SL 5.08HC/180G

Pin headers in glass-fibre-reinforced plastic with straight wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SL 5.08HC/08/180G 3.2SN... | Version |
| Order No. | 1148830000 | PCB plug-in connector, male header, closed side, THT solder |
| GTIN (EAN) | 4032248107285 | connection, 5.08 mm, Number of poles: 8, 180°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |
| Type | SL 5.08HC/08/180G 3.2SN... | Version |
| Order No. | 1146870000 | PCB plug-in connector, male header, closed side, THT solder |
| GTIN (EAN) | 4032248932900 | connection, 5.08 mm, Number of poles: 8, 180°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, orange, Box |

SL 5.08HC/90

Pin headers made from glass-fibre-reinforced plastic with 90° wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.


General ordering data

| | | |
|------------|----------------------------|--|
| Type | SL 5.08HC/08/90 3.2SN B... | Version |
| Order No. | 1155090000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4050118050752 | connection, 5.08 mm, Number of poles: 8, 90°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |
| Type | SL 5.08HC/08/90 3.2SN O... | Version |
| Order No. | 1146850000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4050118051445 | connection, 5.08 mm, Number of poles: 8, 90°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, orange, Box |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Counterpart**SL 5.08HC/90B**

Pin headers made from glass-fibre-reinforced plastic with 90° wire outlet; optimised for wave soldering. The flange variant (F) can be screwed onto the respective counter piece or the circuit board. There is no need for an extra screw to connect the circuit board when the solder flange (LF) version is used. This also protects the solder points from mechanical strain. All pin headers can be manually coded or ordered pre-coded. HC = High Current.

General ordering data


| | | |
|------------|----------------------------|--|
| Type | SL 5.08HC/08/90B 3.2SN ... | Version |
| Order No. | 1155640000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4050118050295 | solder connection, 5.08 mm, Number of poles: 8, 90°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, black, Box |
| Type | SL 5.08HC/08/90B 3.2SN ... | Version |
| Order No. | 1154830000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4050118050981 | solder connection, 5.08 mm, Number of poles: 8, 90°, Solder pin |
| Qty. | 50 ST | length (l): 3.2 mm, tinned, orange, Box |

SLDV 5.08/180

Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SLD 5.08V/16/180 3.2SN ... | Version |
| Order No. | 1725710000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4032248062003 | connection, 5.08 mm, Number of poles: 16, 180°, Solder pin length |
| Qty. | 20 ST | (l): 3.2 mm, tinned, orange, Box |

SLDV 5.08/180B

Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.


BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart**General ordering data**

| | | |
|------------|----------------------------|--|
| Type | SLD 5.08V/16/180B 3.2SN... | Version |
| Order No. | 1726800000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248062683 | solder connection, 5.08 mm, Number of poles: 16, 180°, Solder pin |
| Qty. | 20 ST | length (l): 3.2 mm, tinned, orange, Box |

SLDV 5.08/90

Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SLD 5.08V/16/90 3.2 SN ... | Version |
| Order No. | 1725230000 | PCB plug-in connector, male header, open side, THT solder |
| GTIN (EAN) | 4032248060634 | connection, 5.08 mm, Number of poles: 16, 90°, Solder pin length (l): |
| Qty. | 20 ST | 3.2 mm, tinned, orange, Box |

SLDV 5.08/90B

Pin headers with solder pin length optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. HC = High Current.


General ordering data

| | | |
|------------|----------------------------|--|
| Type | SLD 5.08V/16/90B 3.2 SN... | Version |
| Order No. | 1726340000 | PCB plug-in connector, male header, Dovetails for fixing blocks, THT |
| GTIN (EAN) | 4032248061310 | solder connection, 5.08 mm, Number of poles: 16, 90°, Solder pin |
| Qty. | 20 ST | length (l): 3.2 mm, tinned, orange, Box |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Counterpart**SL-SMT 5.08/180 Box**

High-temperature-resistant, straight, open pin header. Packed in box or tape. On tape and with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data


| | | |
|------------|----------------------------|---|
| Type | SL-SMT 5.08HC/08/180 1.... | Version |
| Order No. | 1775662001 | PCB plug-in connector, male header, open side, THT/THR solder |
| GTIN (EAN) | 4032248157600 | connection, 5.08 mm, Number of poles: 8, 180°, Solder pin length (l): |
| Qty. | 50 ST | 1.5 mm, tinned, black, Box |
| Type | SL-SMT 5.08HC/08/180 3.... | Version |
| Order No. | 1838040000 | PCB plug-in connector, male header, open side, THT/THR solder |
| GTIN (EAN) | 4032248348107 | connection, 5.08 mm, Number of poles: 8, 180°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |

SL-SMT 5.08/180 Tape

High-temperature-resistant, straight, open pin header. Packed in box or tape. On tape and with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SL-SMT 5.08HC/08/180 1.... | Version |
| Order No. | 1775664001 | PCB plug-in connector, male header, open side, THT/THR solder |
| GTIN (EAN) | 4032248159642 | connection, 5.08 mm, Number of poles: 8, 180°, Solder pin length (l): |
| Qty. | 250 ST | 1.5 mm, tinned, black, Tape |

SL-SMT 5.08/180G Box

High-temperature-resistant pin header, packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.


BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart**General ordering data**

| | | |
|------------|----------------------------|---|
| Type | SL-SMT 5.08HC/08/180G 1... | Version |
| Order No. | 1775982001 | PCB plug-in connector, male header, closed side, THT/THR solder |
| GTIN (EAN) | 4032248158973 | connection, 5.08 mm, Number of poles: 8, 180°, Solder pin length (l): |
| Qty. | 50 ST | 1.5 mm, tinned, black, Box |
| Type | SL-SMT 5.08HC/08/180G 3... | Version |
| Order No. | 1838270000 | PCB plug-in connector, male header, closed side, THT/THR solder |
| GTIN (EAN) | 4032248348336 | connection, 5.08 mm, Number of poles: 8, 180°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |

SL-SMT 5.08/270GH Box

High-temperature-resistant, straight, open pin header. Packed in box or tape. On tape and with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SL-SMT 5.08HC/08/270GH ... | Version |
| Order No. | 1877080000 | PCB plug-in connector, male header, closed side, THT/THR solder |
| GTIN (EAN) | 4032248467563 | connection, 5.08 mm, Number of poles: 8, 270°, Solder pin length (l): |
| Qty. | 50 ST | 1.5 mm, tinned, black, Box |
| Type | SL-SMT 5.08HC/08/270GH ... | Version |
| Order No. | 1877450000 | PCB plug-in connector, male header, closed side, THT/THR solder |
| GTIN (EAN) | 4032248468065 | connection, 5.08 mm, Number of poles: 8, 270°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |

SL-SMT 5.08/270GH Tape

High-temperature-resistant, straight, open pin header. Packed in box or tape. On tape and with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SL-SMT 5.08HC/08/270GH ... | Version |
| Order No. | 1877650000 | PCB plug-in connector, male header, closed side, THT/THR solder |
| GTIN (EAN) | 4032248468249 | connection, 5.08 mm, Number of poles: 8, 270°, Solder pin length (l): |
| Qty. | 285 ST | 1.5 mm, tinned, black, Tape |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart**SL-SMT 5.08/270GL Box**

High-temperature-resistant, straight, open pin header. Packed in box or tape. On tape and with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SL-SMT 5.08HC/08/270GL ... | Version |
| Order No. | 1877180000 | PCB plug-in connector, male header, closed side, THT/THR solder |
| GTIN (EAN) | 4032248467839 | connection, 5.08 mm, Number of poles: 8, 270°, Solder pin length (l): |
| Qty. | 50 ST | 1.5 mm, tinned, black, Box |
| Type | SL-SMT 5.08HC/08/270GL ... | Version |
| Order No. | 1877550000 | PCB plug-in connector, male header, closed side, THT/THR solder |
| GTIN (EAN) | 4032248468171 | connection, 5.08 mm, Number of poles: 8, 270°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |

SL-SMT 5.08/270GL Tape

High-temperature-resistant, straight, open pin header. Packed in box or tape. On tape and with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SL-SMT 5.08HC/08/270GL ... | Version |
| Order No. | 1877800000 | PCB plug-in connector, male header, closed side, THT/THR solder |
| GTIN (EAN) | 4032248468454 | connection, 5.08 mm, Number of poles: 8, 270°, Solder pin length (l): |
| Qty. | 350 ST | 1.5 mm, tinned, black, Tape |

SL-SMT 5.08HC/90 Box

High-temperature-resistant, 90° angled, open male header. Packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart**General ordering data**

| | | |
|------------|----------------------------|--|
| Type | SL-SMT 5.08HC/08/90 1.5... | Version |
| Order No. | 1774822001 | PCB plug-in connector, male header, open side, THT/THR solder |
| GTIN (EAN) | 4032248155866 | connection, 5.08 mm, Number of poles: 8, 90°, Solder pin length (l): |
| Qty. | 50 ST | 1.5 mm, tinned, black, Box |
| Type | SL-SMT 5.08HC/08/90 3.2... | Version |
| Order No. | 1780010000 | PCB plug-in connector, male header, open side, THT/THR solder |
| GTIN (EAN) | 4032248165339 | connection, 5.08 mm, Number of poles: 8, 90°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |

SL-SMT 5.08HC/90 Tape

High-temperature-resistant, 90° angled, open male header. Packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SL-SMT 5.08HC/08/90 1.5... | Version |
| Order No. | 1774824001 | PCB plug-in connector, male header, open side, THT/THR solder |
| GTIN (EAN) | 4032248167715 | connection, 5.08 mm, Number of poles: 8, 90°, Solder pin length (l): |
| Qty. | 350 ST | 1.5 mm, tinned, black, Tape |

SL-SMT 5.08HC/90G Box

High-temperature-resistant pin header, packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SL-SMT 5.08HC/08/90G 1.... | Version |
| Order No. | 1775062001 | PCB plug-in connector, male header, closed side, THT/THR solder |
| GTIN (EAN) | 4032248156528 | connection, 5.08 mm, Number of poles: 8, 90°, Solder pin length (l): |
| Qty. | 50 ST | 1.5 mm, tinned, black, Box |
| Type | SL-SMT 5.08HC/08/90G 3.... | Version |
| Order No. | 1780240000 | PCB plug-in connector, male header, closed side, THT/THR solder |
| GTIN (EAN) | 4032248165568 | connection, 5.08 mm, Number of poles: 8, 90°, Solder pin length (l): |
| Qty. | 50 ST | 3.2 mm, tinned, black, Box |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Counterpart**SL-SMT 5.08HC/90G Tape**

High-temperature-resistant pin header, packed in box or tape. On tape, with 1.5 mm solder pin, optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. The pin headers provide space for labelling and can be coded. HC = High Current.

General ordering data


| | | |
|------------|----------------------------|--|
| Type | SL-SMT 5.08HC/08/90G 1... | Version |
| Order No. | 1061940000 | PCB plug-in connector, male header, closed side, THT/THR solder |
| GTIN (EAN) | 4032248811489 | connection, 5.08 mm, Number of poles: 8, 90°, Solder pin length (l): |
| Qty. | 285 ST | 1.5 mm, tinned, black, Tape |

SLF 5.08/180 SN

Male plug with PUSH IN wire connection and straight outlet direction, when used with BLF 5.08HC as wire-to-wire application for panel feed-through The male plugs provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SLF 5.08/08/180 SN BK BX | Version |
| Order No. | 1335670000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 8, |
| GTIN (EAN) | 4050118139006 | 180°, PUSH IN with actuator, Clamping range, max. : 3.31 mm ² , Box |
| Qty. | 42 ST | |
| Type | SLF 5.08/08/180 SN OR BX | Version |
| Order No. | 1335390000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 8, |
| GTIN (EAN) | 4050118138665 | 180°, PUSH IN with actuator, Clamping range, max. : 3.31 mm ² , Box |
| Qty. | 42 ST | |

SLF 5.08/180B SN

Male plug with PUSH IN wire connection and straight outlet direction, when used with BLF 5.08HC as wire-to-wire application for panel feed-through The male plugs provide space for labelling and can be coded.

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart**General ordering data**

| | | |
|------------|----------------------------|---|
| Type | SLF 5.08/08/180B SN BK ... | Version |
| Order No. | 1335900000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 8, 180°, PUSH IN with actuator, Clamping range, max. : 3.31 mm ² , Box |
| GTIN (EAN) | 4050118139303 | |
| Qty. | 42 ST | |
| Type | SLF 5.08/08/180B SN OR ... | Version |
| Order No. | 1335510000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 8, 180°, PUSH IN with actuator, Clamping range, max. : 3.31 mm ² , Box |
| GTIN (EAN) | 4050118140125 | |
| Qty. | 42 ST | |

SLF 5.08/180DF SN

Male plug with PUSH IN wire connection and straight outlet direction, when used with BLF 5.08HC as wire-to-wire application for panel feed-through. The male plugs provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SLF 5.08/08/180DF SN OR... | Version |
| Order No. | 1353650000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 8, 180°, PUSH IN with actuator, Clamping range, max. : 3.31 mm ² , Box |
| GTIN (EAN) | 4050118156379 | |
| Qty. | 24 ST | |

SLT 5.08/180DF SN

Male plugs with screw TOP wire connection. The male plug provides space for labelling and can be coded.


General ordering data

| | | |
|------------|----------------------------|---|
| Type | SLT 5.08/08/180DF SN OR... | Version |
| Order No. | 1353430000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 8, 180°, TOP connection, Clamping range, max. : 2.5 mm ² , Box |
| GTIN (EAN) | 4050118155891 | |
| Qty. | 24 ST | |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Counterpart**SLT 5.08B**

Male plugs with screw TOP wire connection. The male plug provides space for labelling and can be coded.

General ordering data


| | | |
|------------|----------------------------|--|
| Type | SLT 5.08/08/180B SN OR ... | Version |
| Order No. | 1611770000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 8, |
| GTIN (EAN) | 4008190192655 | 180°, TOP connection, Clamping range, max. : 2.5 mm ² , Box |
| Qty. | 50 ST | |

SLS 5.08/180 SN

Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SLS 5.08/08/180 SN OR BX | Version |
| Order No. | 1627150000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 8, |
| GTIN (EAN) | 4008190199661 | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm ² , |
| Qty. | 42 ST | Box |

SLS 5.08/180B

Male plugs with clamping-yoke screw wire-connect system. The male plugs provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SLS 5.08/08/180B SN OR ... | Version |
| Order No. | 1627300000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 8, |
| GTIN (EAN) | 4008190199814 | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm ² , |
| Qty. | 42 ST | Box |

BLC 5.08/08/180R BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart**SLS 5.08TB KF35**

Male plugs with clamping-yoke screw wire-connect system. With clip-on feet for attaching the male plugs on rail. The male plugs provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SLS 5.08/08/180TB KF SN... | Version |
| Order No. | 1846150000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 8, |
| GTIN (EAN) | 4032248362431 | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm ² , |
| Qty. | 10 ST | Box |

SLS 5.08TB RF15

Male plugs with clamping-yoke screw wire-connect system. With clip-on feet for attaching the male plugs on rail. The male plugs provide space for labelling and can be coded.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SLS 5.08/08/180TB RF15 ... | Version |
| Order No. | 1846070000 | PCB plug-in connector, male plug, 5.08 mm, Number of poles: 8, |
| GTIN (EAN) | 4032248362356 | 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm ² , |
| Qty. | 10 ST | Box |