


## LM WO 25/140 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

### General ordering data

|            |  |
|------------|--|
| Version    | LaserMark, Conductor and cable markers, 16.2 - 36.4 mm, 25 x 140 mm, white |
| Order No.  | <a href="#">1712491044</a>   |
| Type       | LM WO 25/140 WS  |
| GTIN (EAN) | 4008190947118  |
| Qty.       | 10 items   |

## LM WO 25/140 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.03 mm | Depth (inches)  | 0.001 inch  |
| Height     | 25 mm   | Height (inches) | 0.9842 inch |
| Width      | 140 mm  | Width (inches)  | 5.5118 inch |
| Net weight | 10.2 g  |                 |             |

## Temperatures

Operating temperature range -40...150 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

## General data

|  |  |             |
|--|--|-------------|
| Adhesive                                     | Acrylate                                       |             |
| Material colour according to resistance code | 9  |             |
| Number per sheet                             | 16   |             |
| Type of printing                             | neutral  |             |
| Version                                      | Self-adhesive                                  |             |
| Width  | 140 mm   |             |
| UL 94 flammability rating                    | V-0  |             |
| Operating temperature range, max.            | 150 °C   |             |
| Operating temperature range, min.            | -40 °C   |             |
| Colour                                       | white  |             |
| Halogen                                      | No   |             |
| Basic material                               | Polyester film                                 |             |
| Printed characters                           | without  |             |
| Number of markers per packaging unit         | 160  |             |
| Number of markers per packaging unit         | Form of supply                                 | Label sheet |
|  | Number of combinations per packaging unit      | 10          |
|  | Number of markers per combination              | 16          |
| Size of labelling field                      | 25 x 26 mm                                     |             |
| Number of markers per combination            | 1 Label sheet = 16 Conductor and cable markers |             |
| Operating temperature range                  | -40...150 °C                                   |             |

## Conductor and cable markers

|                                  |                          |                               |                     |
|----------------------------------|--------------------------|-------------------------------|---------------------|
| Halogen                          | No                       | Conductor cross-section, max. | 150 mm <sup>2</sup> |
| Conductor cross-section, min.    | 70 mm <sup>2</sup>       | Conductor O.D., max.          | 36.4 mm             |
| Conductor O.D., min.             | 16.2 mm                  | Text field width              | 25 mm               |
| Text field height                | 26 mm                    | Conductor O.D.                | 16.2 - 36.4 mm      |
| Cross-section for connected wire | 70 - 150 mm <sup>2</sup> |                               |                     |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**

