

WSM 10 E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

WSM small plates

- Completely rust-free and acid-resistant
- Embossed characters are still legible when painted
- Also available with custom printing, embossed on a carrier
- Contents of the WSM Service Box, 40 each of: 0-9, A-Ö, +, -, x, /, :, ,, ~, =, ü, Earth, Neutral. 200 steel cable ties (200 mm). 30 stainless steel carriers, 48 mm and 60 mm; 20 steel carriers, 84 mm, and 10 steel carriers, 108 mm and 288 mm

General ordering data

| | |
|------------|--|
| Version | Stainless steel markers, Conductor and cable markers, 5.5 x 9.9 mm, silver |
| Order No. | 1712501645 |
| Type | WSM 10 E |
| GTIN (EAN) | 4008190947323 |
| Qty. | 200 items |

WSM 10 E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 0.3 mm | Depth (inches) | 0.0118 inch |
| Height | 5.5 mm | Height (inches) | 0.2165 inch |
| Width | 9.9 mm | Width (inches) | 0.3898 inch |
| Net weight | 0.15 g | | |

Temperatures

| | |
|-----------------------------|--------|
| Operating temperature range | 500 °C |
|-----------------------------|--------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | |
|--------------------------------------|--|----------------|
| Orientation of print | horizontal | |
| Type of printing | Standard | |
| Width | 9.9 mm | |
| Operating temperature range, max. | 500 °C | |
| Colour | silver | |
| Halogen | No | |
| Basic material | Stainless steel 1.4404 | |
| Printed characters | Upper-case letters | |
| Number of markers per packaging unit | Form of supply | Component part |
| Number of markers per combination | 1 Component part = Conductor and cable markers | |
| Operating temperature range | 500 °C | |
| Imprint | E | |

Conductor and cable markers

| | | | |
|-------------------------------|--------------------|----------------------------------|--------------------------|
| Halogen | No | Conductor cross-section, max. | 500 mm ² |
| Conductor cross-section, min. | 16 mm ² | Cross-section for connected wire | 16 - 500 mm ² |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |