

## WSM 10 NEUTRAL

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

Advantages:

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

### General ordering data

|            |  |
|------------|--|
| Version    | Stainless steel markers, Conductor and cable markers, 14 - 79 mm, 5.5 x 9.9 mm, silver |
| Order No.  | <a href="#">1712502000</a>   |
| Type       | WSM 10 NEUTRAL   |
| GTIN (EAN) | 4032248052844  |
| Qty.       | 200 items  |

## WSM 10 NEUTRAL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 0.3 mm | Depth (inches)  | 0.0118 inch |
| Height     | 5.5 mm | Height (inches) | 0.2165 inch |
| Width      | 9.9 mm | Width (inches)  | 0.3898 inch |
| Net weight | 0.13 g |                 |             |

## Temperatures

Operating temperature range 250 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

## General data

|                                      |  |
|--------------------------------------|--|
| Number per sheet                     | 200  |
| Type of printing                     | neutral  |
| Width                                | 9.9 mm   |
| Operating temperature range, max.    | 250 °C   |
| Colour                               | silver   |
| Basic material                       | Stainless steel 1.4404                         |
| Printed characters                   | without  |
| Number of markers per packaging unit | Form of supply Component part                  |
| Number of markers per combination    | 1 Component part = Conductor and cable markers |
| Operating temperature range          | 250 °C   |

## Conductor and cable markers

|                               |                     |                                  |                          |
|-------------------------------|---------------------|----------------------------------|--------------------------|
| Conductor cross-section, max. | 500 mm <sup>2</sup> | Conductor cross-section, min.    | 16 mm <sup>2</sup>       |
| Conductor O.D., max.          | 79 mm               | Conductor O.D., min.             | 14 mm                    |
| Conductor O.D.                | 14 - 79 mm          | Cross-section for connected wire | 16 - 500 mm <sup>2</sup> |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |