

HDC-KIT-HE 16.120

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The wire connection level is designed as a screw element. All screw connections are equipped with a wire protection spring.

General ordering data

Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HE, Installation size: 6, Poles: 16, Screw connection, 500 V, 16 A, diecast aluminium, PG 21
Order No.	1712520000
Type	HDC-KIT-HE 16.120
GTIN (EAN)	4008190947743
Qty.	1 items

HDC-KIT-HE 16.120

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 626.68 g

Temperatures

Limit temperature -40 °C ... 100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3

SCIP bfb1c983-6f18-4ba4-8907-38aad6aee076

General data

UL 94 flammability rating	V-0	Surface finish	Powder coating
Protection degree	IP65	Series	HE

Version

Size of cable entries	PG 21	Number of cable entry on top	0
Number of cable entry sideways	1	Type of connection	Screw connection
Design of locking system	Side-locking clamp on lower side	Installation size	6
Type	Male, Female	Sealing	NBR
Colour (RAL)	RAL 7035	BG	6

General data

Number of poles	16	Connection type PE	Screw connection
Installation size	6	Cable gland	PG 21
Basic material	diecast aluminium	Series	HE
Rated voltage (DIN EN 61984)	500 V	Rated current (DIN EN 61984)	16 A
BG	6		

Version

Type of connection	Screw connection	Installation size	6
Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Surface finish	Powder coating	Max. torque for main contact	0.55 Nm
Basic material	diecast aluminium	Min. torque for main contact	0.5 Nm
BG	6		

Classifications

ETIM 8.0	EC002636	ETIM 9.0	EC002636
ETIM 10.0	EC002636	ECLASS 14.0	27-44-01-13

Technical data

ECLASS 15.0

27-44-01-13
