

VT-TM 2/18 HF**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The TM sleeves contain no halogens and virtually no pollutants. The sleeves are equipped with the TM-I 12 or TM-I 18 tags. They cover a wide range of applications for cables and lines. This system has particularly proved its worth in traffic engineering. The slim design guarantees firm seating on the conductor.

- Halogen-free
- The slim design guarantees firm seating on the conductor
- TMX 18 for mounting with cable-ties (width 3.6 mm)

General ordering data

Version	TM, Socket x 6.4 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.: 2.5 - 4 mm
Order No.	1714240000
Type	VT-TM 2/18 HF
GTIN (EAN)	4008190332907
Qty.	2000 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	18 mm	Height (inches)	0.7087 inch
Width	6.4 mm	Width (inches)	0.252 inch
Net weight	0.25 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.001 kg CO2 eq.	

General data

Type of printing	neutral	Width	6.4 mm
UL 94 flammability rating	HB	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Colour	Transparent
Halogen	No	Basic material	Polyethylene LD
Recommended industries	Transportation, Machinery	Operating temperature range	-40...80 °C

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	0.75 mm ²	Conductor O.D., max.	4 mm
Conductor O.D., min.	2.5 mm	Conductor O.D.	2.5 - 4 mm
Cross-section for connected wire	0.75 - 2.5 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		