

**DFFC .5-1.0 ZRV1.5****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Crimp contact (terminal), 1.5 mm <sup>2</sup>
Order No.	<a href="#">1705320000</a>
Type	DFFC .5-1.0 ZRV1.5
GTIN (EAN)	4008190948566
Qty.	500 items

## DFFC .5-1.0 ZRV1.5

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Net weight	0.22 g
------------	--------

## Temperatures

Ambient temperature	-5 °C...40 °C	Operating temperature	130 °C
---------------------	---------------	-----------------------	--------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Plastic	Surface finish	tinned
Colour	silver		

## System specifications

Version	for holding 0.5 ... 1.0 mm <sup>2</sup>
---------	---

## Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

## Conductors for clamping (rated connection)

Stripping length	6 mm	Type of connection	Crimp contact
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	1 mm <sup>2</sup>

## General

Installation advice	Direct mounting	Surface finish	tinned
---------------------	-----------------	----------------	--------

## Rating data

Rated cross-section	1.5 mm <sup>2</sup>	Volume resistance according to IEC 60947-7-x	1.83 mΩ
Power loss in accordance with IEC 60947-7-x	0.56 W		

## Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		