

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	EWS (drainage device), Compensating element, M 25, 5 mm, Polyamide
Order No.	1719740000
Type	EWS M 25X1,5
GTIN (EAN)	4008190353001
Qty.	20 items

EWS M 25X1,5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	23 mm	Height (inches)	0.9055 inch
Length	23 mm	Length (inches)	0.9055 inch
Net weight	13.25 g		

Temperatures

Operating temperature	-20 °C...40 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Certificate numbers cable gland

Identification	Ex e II, II 2 GD	Certificate no. cable gland (ATEX)	PTB 01 ATEX 1128 X
----------------	------------------	------------------------------------	--------------------

General information

UL 94 flammability rating	V-2	Operating temperature range, max.	40 °C
Operating temperature range, min.	-20 °C	Pitch of thread	1.5 mm
AF size 1	30 mm	Protection degree	IP54
Cable gland	metric	Basic material	Polyamide
External thread	M 25	Length of thread	5 mm
Inside diameter D2	25.00 mm	Torque for connecting adapter, max.	5.00 Nm
Torque for connecting adapter, min.	5.00 Nm		

Classifications

ETIM 8.0	EC000814	ETIM 9.0	EC000814
ETIM 10.0	EC000814	ECLASS 14.0	27-18-28-17
ECLASS 15.0	27-18-28-17		

Drawings

