

## ZDL 2.5 S/L/L/PE

**Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



#### Building installation wiring

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

#### General ordering data

|                     |  |
|---------------------|--|
| Version             | Z-series, Installation multi-tier terminal, Rated cross-section: 2.5 mm <sup>2</sup> , Tension-clamp connection, dark beige, Direct mounting |
| Order No.           | <a href="#">1720810000</a>   |
| Type                | ZDL 2.5 S/L/L/PE   |
| GTIN (EAN)          | 4008 190380366   |
| Qty.                | 50 items   |
| Delivery status     | This article will no longer be available in the future.  |
| Available until     | 2023-03-31T00:00:00+02:00  |
| Alternative product | <a href="#">AITB 2.5 BB L-L-PE</a>   |

## ZDL 2.5 S/L/L/PE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E60693

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 48 mm   | Depth (inches)  | 1.8898 inch |
| Height     | 95 mm   | Height (inches) | 3.7401 inch |
| Width      | 5.1 mm  | Width (inches)  | 0.2008 inch |
| Net weight | 12.21 g |                 |             |

## Temperatures

|                                  |                |                                  |                |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -50 °C...75 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 120 °C         |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Basic material            | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0   |        |            |

## System specifications

|                                     |   |                               |     |
|-------------------------------------|---|-------------------------------|-----|
| Version                             | 3-conductor installation terminal, Tension-clamp connection, With PE connection, for plug-in cross-connector, One end without connector | End cover plate required      | Yes |
| Number of potentials                | 3   | Number of levels              | 2   |
| Number of clamping points per level | 2   | Number of potentials per tier | 1   |
| Levels cross-connected internally   | No  | PE connection                 | Yes |
| Mounting rail                       | TS 35   | N-function                    | No  |
| PE function                         | Yes   | PEN function                  | No  |

## Additional technical data

|                          |       |                     |                 |
|--------------------------|-------|---------------------|-----------------|
| Open sides               | right | Installation advice | Direct mounting |
| Explosion-tested version | No    | Type of mounting    | Snap-on         |

## CSA rating data

|                               |        |                       |                |
|-------------------------------|--------|-----------------------|----------------|
| Wire cross section max. (CSA) | 12 AWG | Certificate No. (CSA) | 154685-1142891 |
| Voltage size D (CSA)          | 300 V  | Current size D (CSA)  | 10 A           |
| Wire cross section min. (CSA) | 26 AWG |                       |                |

## ZDL 2.5 S/L/L/PE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Conductors for clamping (rated connection)

|   |                          |   |                      |
|---|--------------------------|---|----------------------|
| Gauge to IEC 60947-1  | A2                       | Wire connection cross section AWG, max.   | AWG 12               |
| Connection direction  | Inclined / angled        | Stripping length  | 8 mm                 |
| Type of connection  | Tension-clamp connection | Number of connections   | 5                    |
| Clamping range, max.  | 4 mm <sup>2</sup>        | Clamping range, min.  | 0.13 mm <sup>2</sup> |
| Blade size  | 0.6 x 3.5 mm             | Wire connection cross section AWG, min.   | AWG 26               |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm <sup>2</sup>      | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.13 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm <sup>2</sup>      | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.13 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>        | Wire connection cross section, finely stranded, min.                                    | 0.13 mm <sup>2</sup> |
| Connection cross-section, stranded, min.  | 0.13 mm <sup>2</sup>     | Wire connection cross-section, solid core, max.   | 4 mm <sup>2</sup>    |
| Wire connection cross-section, solid core, min.   | 0.13 mm <sup>2</sup>     |   |                      |

### General

|   |        |                     |                      |
|---|--------|---------------------|----------------------|
| Wire connection cross section AWG, max. | AWG 12 | Installation advice | Direct mounting      |
| Wire connection cross section AWG, min. | AWG 26 | Standards           | IEC 60947-7-1 (-7-2) |
| Mounting rail                           | TS 35  |                     |                      |

### Rating data

|  |                     |                                 |                      |
|--|---------------------|---------------------------------|----------------------|
| Rated cross-section                          | 2.5 mm <sup>2</sup> | Rated voltage                   | 400 V                |
| Rated DC voltage                             | 400 V               | Nominal current                 | 24 A                 |
| Current at maximum wires                     | 24 A                | Standards                       | IEC 60947-7-1 (-7-2) |
| Volume resistance according to IEC 60947-7-x | 1.33 mΩ             | Rated impulse withstand voltage | 4 kV                 |
| Power loss in accordance with IEC 60947-7-x  | 0.77 W              | Pollution severity              | 3                    |


### UL rating data

|   |        |                      |        |
|---|--------|----------------------|--------|
| Voltage size B (UR)                     | 300 V  | Current size B (UR)  | 15 A   |
| Conductor size Factory wiring max. (UR) | 12 AWG | Current size D (UR)  | 10 A   |
| Conductor size Factory wiring min. (UR) | 26 AWG | Certificate No. (UR) | E60693 |
| Conductor size Field wiring min. (UR)   | 26 AWG | Voltage size D (UR)  | 300 V  |
| Conductor size Field wiring max. (UR)   | 12 AWG |                      |        |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001329    | ETIM 9.0    | EC001329    |
| ETIM 10.0   | EC001329    | ECLASS 14.0 | 27-25-01-10 |
| ECLASS 15.0 | 27-25-01-10 |             |             |

Drawings



## ZDL 2.5 S/L/L/PE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### General ordering data

|            |                            |                                 |
|------------|----------------------------|---------------------------------|
| Type       | ZQV 2.5N/2 GE              | Version                         |
| Order No.  | <a href="#">1693800000</a> | W-Series, Cross-connector, 24 A |
| GTIN (EAN) | 4008190883621              |                                 |
| Qty.       | 60 ST                      |                                 |
| Type       | ZQV 2.5N/3 GE              | Version                         |
| Order No.  | <a href="#">1693810000</a> | W-Series, Cross-connector, 24 A |
| GTIN (EAN) | 4008190883645              |                                 |
| Qty.       | 60 ST                      |                                 |
| Type       | ZQV 2.5N/4 GE              | Version                         |
| Order No.  | <a href="#">1693820000</a> | W-Series, Cross-connector, 24 A |
| GTIN (EAN) | 4008190883652              |                                 |
| Qty.       | 60 ST                      |                                 |
| Type       | ZQV 2.5N/5 GE              | Version                         |
| Order No.  | <a href="#">1693830000</a> | W-Series, Cross-connector, 24 A |
| GTIN (EAN) | 4008190883669              |                                 |
| Qty.       | 20 ST                      |                                 |
| Type       | ZQV 2.5N/6 GE              | Version                         |
| Order No.  | <a href="#">1693840000</a> | W-Series, Cross-connector, 24 A |
| GTIN (EAN) | 4008190883676              |                                 |
| Qty.       | 20 ST                      |                                 |
| Type       | ZQV 2.5N/7 GE              | Version                         |
| Order No.  | <a href="#">1693850000</a> | W-Series, Cross-connector, 24 A |
| GTIN (EAN) | 4008190883683              |                                 |
| Qty.       | 20 ST                      |                                 |
| Type       | ZQV 2.5N/8 GE              | Version                         |
| Order No.  | <a href="#">1693860000</a> | W-Series, Cross-connector, 24 A |
| GTIN (EAN) | 4008190883690              |                                 |
| Qty.       | 20 ST                      |                                 |
| Type       | ZQV 2.5N/9 GE              | Version                         |
| Order No.  | <a href="#">1693870000</a> | W-Series, Cross-connector, 24 A |
| GTIN (EAN) | 4008190883706              |                                 |
| Qty.       | 20 ST                      |                                 |
| Type       | ZQV 2.5N/10 GE             | Version                         |
| Order No.  | <a href="#">1693880000</a> | W-Series, Cross-connector, 24 A |
| GTIN (EAN) | 4008190883720              |                                 |
| Qty.       | 20 ST                      |                                 |
| Type       | ZQV 2.5N/20 GE             | Version                         |
| Order No.  | <a href="#">1909000000</a> | W-Series, Cross-connector, 24 A |
| GTIN (EAN) | 4032248535613              |                                 |
| Qty.       | 20 ST                      |                                 |

## ZDL 2.5 S/L/L/PE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |                                 |
|------------|----------------------------|---------------------------------|
| Type       | ZQV 2.5N/50 GE             | Version                         |
| Order No.  | <a href="#">1693890000</a> | W-Series, Cross-connector, 24 A |
| GTIN (EAN) | 4008190883737              |                                 |
| Qty.       | 5 ST                       |                                 |

## End plates and partition plates




Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

## General ordering data

|            |                            |                     |
|------------|----------------------------|---------------------|
| Type       | ZAP ZDL2.5S                | Version             |
| Order No.  | <a href="#">1720900000</a> | Z-series, End plate |
| GTIN (EAN) | 4008190381059              |                     |
| Qty.       | 20 ST                      |                     |

## End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | EW 35                      | Version  |
| Order No.  | <a href="#">0383560000</a> | End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C     |
| GTIN (EAN) | 4008190181314              |  |
| Qty.       | 50 ST                      |  |
| Type       | EW 35/SCHA/M3              | Version  |
| Order No.  | <a href="#">0258660000</a> | End bracket, beige, TS 35, V-2, Wemid, Width: 16.5 mm, 100 °C    |
| GTIN (EAN) | 4008190033477              |  |
| Qty.       | 20 ST                      |  |
| Type       | WEW 35/1                   | Version  |
| Order No.  | <a href="#">1059000000</a> | End bracket, dark beige, TS 35, V-2, Wemid, Width: 12 mm, 100 °C |
| GTIN (EAN) | 4008190172282              |  |
| Qty.       | 50 ST                      |  |
| Type       | WEW 35/2                   | Version  |
| Order No.  | <a href="#">1061200000</a> | End bracket, dark beige, TS 35, HB, Wemid, Width: 8 mm, 100 °C   |
| GTIN (EAN) | 4008190030230              |  |
| Qty.       | 50 ST                      |  |

## ZDL 2.5 S/L/L/PE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |   |
|------------|----------------------------|---|
| Type       | ZEW 35                     | Version   |
| Order No.  | <a href="#">9540000000</a> | End bracket, dark beige, TS 35, V-2, Wemid, Width: 6 mm, 100 °C |
| GTIN (EAN) | 4008190956264              |   |
| Qty.       | 20 ST                      |   |
| Type       | ZEW 35/2                   | Version   |
| Order No.  | <a href="#">8630740000</a> | End bracket, dark beige, TS 35, V-2, Wemid, Width: 8 mm, 100 °C |
| GTIN (EAN) | 4032248348916              |   |
| Qty.       | 20 ST                      |   |

## Busbar connections



Weidmüller offers tapping terminals for various types of bus bar systems. Depending on the application, a distinction can be made here between insulated and non-insulated tap-off terminals.

## General ordering data

|            |                            |                              |
|------------|----------------------------|------------------------------|
| Type       | ZB 4                       | Version                      |
| Order No.  | <a href="#">0316500000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190061999              |                              |
| Qty.       | 50 ST                      |                              |
| Type       | ZB 4G BL                   | Version                      |
| Order No.  | <a href="#">0322180000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190050504              |                              |
| Qty.       | 50 ST                      |                              |
| Type       | ZB 4K GE/GN                | Version                      |
| Order No.  | <a href="#">0475360000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190188047              |                              |
| Qty.       | 50 ST                      |                              |
| Type       | ZB 4K GG HENSEL            | Version                      |
| Order No.  | <a href="#">1824560000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4032248330973              |                              |
| Qty.       | 50 ST                      |                              |
| Type       | ZB 4K SW                   | Version                      |
| Order No.  | <a href="#">0475310000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190008406              |                              |
| Qty.       | 50 ST                      |                              |
| Type       | ZB 4/6                     | Version                      |
| Order No.  | <a href="#">0556700000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190188412              |                              |
| Qty.       | 50 ST                      |                              |
| Type       | ZB 4/6K BL                 | Version                      |
| Order No.  | <a href="#">0565480000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190086831              |                              |
| Qty.       | 50 ST                      |                              |

## ZDL 2.5 S/L/L/PE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |                              |
|------------|----------------------------|------------------------------|
| Type       | ZB 16K BL                  | Version                      |
| Order No.  | <a href="#">0502880000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190014186              |                              |
| Qty.       | 50 ST                      |                              |
| Type       | ZB 4/6K GE/GN              | Version                      |
| Order No.  | <a href="#">0565460000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190032609              |                              |
| Qty.       | 50 ST                      |                              |
| Type       | ZB 16K GE/GN               | Version                      |
| Order No.  | <a href="#">0502860000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190188795              |                              |
| Qty.       | 50 ST                      |                              |
| Type       | ZB 16K SW                  | Version                      |
| Order No.  | <a href="#">0502810000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190332563              |                              |
| Qty.       | 50 ST                      |                              |
| Type       | ZB 16 ZKSC                 | Version                      |
| Order No.  | <a href="#">0316600000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190145989              |                              |
| Qty.       | 50 ST                      |                              |
| Type       | ZB 35/M6X16                | Version                      |
| Order No.  | <a href="#">0266500000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190102814              |                              |
| Qty.       | 20 ST                      |                              |
| Type       | ZB 35K GE/GN M6X16         | Version                      |
| Order No.  | <a href="#">0502660000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190052294              |                              |
| Qty.       | 20 ST                      |                              |
| Type       | ZB 35K SW M6X16            | Version                      |
| Order No.  | <a href="#">0502610000</a> | Terminal (busbar connection) |
| GTIN (EAN) | 4008190332587              |                              |
| Qty.       | 20 ST                      |                              |

## Busbars



With our bus bars in various materials and the associated accessories, you can connect cables in the smallest installation space. Depending on the application, potentials can be collected, distributed or dissipated.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | SSCH 10X3X1000 CU/SN       | Version   |
| Order No.  | <a href="#">0348900000</a> | Busbar (terminal), silver, Height: 1000 mm, Depth: 3 mm, Copper |
| GTIN (EAN) | 4008190024802              |   |
| Qty.       | 25 M                       |   |

## ZDL 2.5 S/L/L/PE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | DEK 5/5 MC SDR             | Version   |
| Order No.  | <a href="#">1609810000</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190456597              | Weidmueller, To customer specification                    |
| Qty.       | 200 ST                     |   |

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | BZT 1 WS 10/5              | Version                    |
| Order No.  | <a href="#">1805490000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231              |                            |
| Qty.       | 100 ST                     |                            |
| Type       | BZT 1 ZA WS 10/5           | Version                    |
| Order No.  | <a href="#">1805520000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248              |                            |
| Qty.       | 100 ST                     |                            |


## ZDL 2.5 S/L/L/PE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

### General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | SDIS SLIM 0.6X3.5X100      | Version   |  |
| Order No.  | <a href="#">2749610000</a> | Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |  |
| GTIN (EAN) | 4050118896350              | thickness (A): 0.6 mm   |  |
| Qty.       | 1 ST                       |   |  |