

## HDC-KIT-HSB 06.500

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The RockStar® kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard plug-in connector combinations with metric or PG cable entry threads, with screw connection or PUSH IN connection.

### General ordering data

Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HSB, Installation size: 6, Poles: 6, Screw connection, 400 V, 35 A, diecast aluminium, PG 21
Order No.	<a href="#">1724000000</a>
Type	HDC-KIT-HSB 06.500
GTIN (EAN)	4008190367770
Qty.	1 items

## HDC-KIT-HSB 06.500

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Net weight 596.68 g

## Temperatures

Limit temperature -40 °C ... 100 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3

SCIP bfb1c983-6f18-4ba4-8907-38aad6aee076

## General data

Surface finish	Powder coating	Protection degree	IP65
Series	HSB		

## Version

Size of cable entries	PG 21	Number of cable entry on top	0
Number of cable entry sideways	1	Type of connection	Screw connection
Design of locking system	Side-locking clamp on lower side	Installation size	6
Sealing	NBR	Colour (RAL)	RAL 7035
BG	6		

## General data

Number of poles	6	Connection type PE	Screw connection
Installation size	6	Cable gland	PG 21
Basic material	diecast aluminium	Series	HSB
Rated voltage (DIN EN 61984)	400 V	Rated current (DIN EN 61984)	35 A
BG	6		

## Version

Type of connection	Screw connection	Installation size	6
Conductor cross-section, max.	6 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Surface finish	Powder coating	Max. torque for main contact	1.5 Nm
Basic material	diecast aluminium	Min. torque for main contact	1.2 Nm
BG	6		

## Classifications

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92

**Technical data**

---

ECLASS 15.0

27-44-02-92

---

**HDC-KIT-HSB 06.500**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**HDC COS**

Various accessories are available for our inserts. This includes coding elements for the inserts.



**General ordering data**

Type	HDC COS 16	Version
Order No.	<a href="#">1431000000</a>	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190052706	
Qty.	1 ST	
Type	HDC COS 24	Version
Order No.	<a href="#">1430900000</a>	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190077228	
Qty.	1 ST	
Type	HDC COS 32	Version
Order No.	<a href="#">1430800000</a>	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190176181	
Qty.	1 ST	

**SPB**

Various accessories are available for our inserts. This includes coding elements for the inserts.



**General ordering data**

Type	SPB-M 3	Version
Order No.	<a href="#">1203600000</a>	Heavy-duty connectors, Accessories, Lock bolts
GTIN (EAN)	4008190120047	
Qty.	100 ST	