


## LM MT300 30/20 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

### General ordering data

|            |   |
|------------|---|
| Version    | LaserMark, Device markers, 20 x 30 mm, yellow |
| Order No.  | <a href="#">1724161687</a>                    |
| Type       | LM MT300 30/20 GE                             |
| GTIN (EAN) | 4008 190369026                                |
| Qty.       | 10 items                                      |

## LM MT300 30/20 GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.08 mm | Depth (inches)  | 0.0031 inch |
| Height     | 20 mm   | Height (inches) | 0.7874 inch |
| Width      | 30 mm   | Width (inches)  | 1.1811 inch |
| Net weight | 11.5 g  |                 |             |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|  |   |             |  |
|--|---|-------------|--|
| Adhesive                                     | Acrylate adhesive                         |             |  |
| Material colour according to resistance code | 4   |             |  |
| Number per sheet                             | 78  |             |  |
| Printing method                              | Laser print                               |             |  |
| Version                                      | Self-adhesive                             |             |  |
| Width  | 30 mm                                     |             |  |
| UL 94 flammability rating                    | HB  |             |  |
| Operating temperature range, max.            | 150 °C                                    |             |  |
| Operating temperature range, min.            | -40 °C                                    |             |  |
| Colour                                       | yellow                                    |             |  |
| Halogen                                      | No  |             |  |
| Basic material                               | Polyester, PVC-free                       |             |  |
| Printed characters                           | without                                   |             |  |
| Number of markers per packaging unit         | 780                                       |             |  |
| Number of markers per packaging unit         | Form of supply                            | Label sheet |  |
|  | Number of combinations per packaging unit | 10          |  |
|  | Number of markers per combination         | 78          |  |
| Approval acc. to UL 969                      | Yes                                       |             |  |
| Number of markers per combination            | 1 Label sheet = 78 Device markers         |             |  |
| Operating temperature range                  | -40...150 °C                              |             |  |

### Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |

**Drawings**

