

## WSM 10 NEUTRAL

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

Advantages:

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

### General ordering data

Version	Stainless steel markers, Conductor and cable markers, 14 - 79 mm, 5.5 x 9.9 mm, silver
Order No.	<a href="#">1712502000</a>
Type	WSM 10 NEUTRAL
GTIN (EAN)	4032248052844
Qty.	200 items

## WSM 10 NEUTRAL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

Depth	0.3 mm	Depth (inches)	0.0118 inch
Height	5.5 mm	Height (inches)	0.2165 inch
Width	9.9 mm	Width (inches)	0.3898 inch
Net weight	0.13 g		

## Temperatures

Operating temperature range 250 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Number per sheet	200
Type of printing	neutral
Width	9.9 mm
Operating temperature range, max.	250 °C
Colour	silver
Basic material	Stainless steel 1.4404
Printed characters	without
Number of markers per packaging unit	Form of supply Component part
Number of markers per combination	1 Component part = Conductor and cable markers
Operating temperature range	250 °C

## Conductor and cable markers

Conductor cross-section, max.	500 mm <sup>2</sup>	Conductor cross-section, min.	16 mm <sup>2</sup>
Conductor O.D., max.	79 mm	Conductor O.D., min.	14 mm
Conductor O.D.	14 - 79 mm	Cross-section for connected wire	16 - 500 mm <sup>2</sup>

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		