


## LM MT300 210/148 SI

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

### General ordering data

Version	LaserMark, Device markers, 148 x 210 mm, silver
Order No.	<a href="#">1724180001</a>
Type	LM MT300 210/148 SI
GTIN (EAN)	4008 190369088
Qty.	10 items

**LM MT300 210/148 SI**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	148 mm	Height (inches)	5.8268 inch
Width	210 mm	Width (inches)	8.2677 inch
Net weight	11.5 g		

**Temperatures**

Operating temperature range -40...150 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Adhesive	Acrylate adhesive		
Number per sheet	2		
Printing method	Laser print		
Version	Self-adhesive		
Width	210 mm		
UL 94 flammability rating	HB		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Colour	silver		
Halogen	No		
Basic material	Polyester, PVC-free		
Printed characters	without		
Number of markers per packaging unit	20		
Number of markers per packaging unit	Form of supply	Label sheet	
	Number of combinations per packaging unit	10	
	Number of markers per combination	2	
Approval acc. to UL 969	Yes		
Number of markers per combination	1 Label sheet = 2 Device markers		
Operating temperature range	-40...150 °C		

**Device markers**

Halogen No

**Classifications**

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**Drawings**

