

## HDC-KIT-HA 03.301

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The wire connection level is designed as a screw element. All screw connections are equipped with a wire protection spring.

### General ordering data

Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HA, Installation size: 1, Poles: 3, Screw connection, 400 V, 16 A, Plastic, PG 11
Order No.	<a href="#">1712570000</a>
Type	HDC-KIT-HA 03.301
GTIN (EAN)	4008190947798
Qty.	1 items

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Net weight 97 g

**Temperatures**

Limit temperature -30 °C ... 80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3

SCIP bfb1c983-6f18-4ba4-8907-38aad6aee076

**General data**

Protection degree	IP65 (in plugged condition)	Series	HA
-------------------	-----------------------------	--------	----

**Version**

Size of cable entries	PG 11	Number of cable entry on top	1
Type of connection	Screw connection	Installation size	1
Colour (RAL)	RAL 7035	BG	1

**General data**

Number of poles	3	Connection type PE	Screw connection
Installation size	1	Cable gland	PG 11
Basic material	Plastic	Series	HA
Rated voltage (DIN EN 61984)	400 V	Rated current (DIN EN 61984)	16 A
BG	1		

**Version**

Type of connection	Screw connection	Installation size	1
Conductor cross-section, max.	2.5 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Max. torque for main contact	0.55 Nm	Basic material	Plastic
Min. torque for main contact	0.5 Nm	BG	1

**Classifications**

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		