

**HDC-KIT-HA 04.401****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The wire connection level is designed as a screw element. All screw connections are equipped with a wire protection spring.

**General ordering data**

Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HA, Installation size: 1, Poles: 4, Screw connection, 400 V, 16 A, Plastic, PG 11
Order No.	<a href="#">1712600000</a>
Type	HDC-KIT-HA 04.401
GTIN (EAN)	4008190947828
Qty.	1 items

## HDC-KIT-HA 04.401

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

Approvals



RoHS Conform

## Dimensions and weights

Net weight 99 g

## Temperatures

Limit temperature -30 °C ... 80 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3

SCIP bfb1c983-6f18-4ba4-8907-38aad6aee076

## General data

Housing main material	Plastic	Protection degree	IP65
Series	HA	EMC housings	No

## Version

Size of cable entries	PG 11	Number of cable entry on top	1
Number of cable entry sideways	0	Type of connection	Screw connection
Design of locking system	Side-locking clamp on lower side	Installation size	1
Sealing	NBR	Colour (RAL)	RAL 7035
BG	1		

## General data

Number of poles	4	Connection type PE	Screw connection
Installation size	1	Cable gland	PG 11
Basic material	Plastic	Series	HA
Rated voltage (DIN EN 61984)	400 V	Rated current (DIN EN 61984)	16 A
BG	1		

## Version

Type of connection	Screw connection	Installation size	1
Conductor cross-section, max.	2.5 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Max. torque for main contact	0.55 Nm	Basic material	Plastic
Min. torque for main contact	0.5 Nm	BG	1

## Classifications

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		