

HDC-KIT-HA 03.403**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The wire connection level is designed as a screw element. All screw connections are equipped with a wire protection spring.

General ordering data

Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HA, Installation size: 1, Poles: 3, Screw connection, 400 V, 16 A, Plastic, PG 11
Order No.	1712630000
Type	HDC-KIT-HA 03.403
GTIN (EAN)	4008190947866
Qty.	1 items

HDC-KIT-HA 03.403

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 104 g

Temperatures

Limit temperature -30 °C ... 80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3

SCIP bfb1c983-6f18-4ba4-8907-38aad6aee076

General data

Surface finish	Powder coating	Protection degree	IP65 (in plugged condition)
Series	HA		

Version

Size of cable entries	PG 11	Number of cable entry on top	1
Type of connection	Screw connection	Installation size	1
Colour (RAL)	RAL 7035	BG	1

General data

Number of poles	3	Connection type PE	Screw connection
Installation size	1	Cable gland	PG 11
Basic material	Plastic	Series	HA
Rated voltage (DIN EN 61984)	400 V	Rated current (DIN EN 61984)	16 A
BG	1		

Version

Type of connection	Screw connection	Installation size	1
Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Surface finish	Powder coating	Max. torque for main contact	0.55 Nm
Basic material	Plastic	Min. torque for main contact	0.5 Nm
BG	1		

Classifications

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		