

VT-TM 3/18 HF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



The TM sleeves contain no halogens and virtually no pollutants. The sleeves are equipped with the TM-I 12 or TM-I 18 tags. They cover a wide range of applications for cables and lines. This system has particularly proved its worth in traffic engineering. The slim design guarantees firm seating on the conductor.

- Halogen-free
- The slim design guarantees firm seating on the conductor
- TMX 18 for mounting with cable-ties (width 3.6 mm)

General ordering data

| | |
|------------|---|
| Version | TM, Socket x 8.1 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.: 4 - 6.5 mm |
| Order No. | 1714260000 |
| Type | VT-TM 3/18 HF |
| GTIN (EAN) | 4008190332921 |
| Qty. | 1000 items |

VT-TM 3/18 HF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 9.3 mm | Depth (inches) | 0.3661 inch |
| Height | 18 mm | Height (inches) | 0.7087 inch |
| Width | 8.1 mm | Width (inches) | 0.3189 inch |
| Net weight | 0.32 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...80 °C |
|-----------------------------|-------------|

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.001 kg CO2 eq. | |

General data

| | | | |
|-----------------------------------|---------------------------|-----------------------------------|-----------------|
| Type of printing | neutral | Width | 8.1 mm |
| UL 94 flammability rating | HB | Operating temperature range, max. | 80 °C |
| Operating temperature range, min. | -40 °C | Colour | Transparent |
| Halogen | No | Basic material | Polyethylene LD |
| Recommended industries | Transportation, Machinery | Operating temperature range | -40...80 °C |

Conductor and cable markers

| | | | |
|----------------------------------|-------------------------|-------------------------------|-------------------|
| Halogen | No | Conductor cross-section, max. | 6 mm ² |
| Conductor cross-section, min. | 2.5 mm ² | Conductor O.D., max. | 6.5 mm |
| Conductor O.D., min. | 4 mm | Conductor O.D. | 4 - 6.5 mm |
| Cross-section for connected wire | 2.5 - 6 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |