

## GWDR PG21-PO

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

### General ordering data

|            |   |
|------------|---|
| Version    | GWDR PO (flat gasket - polyethylene), Sealing ring, PG 21, Polyethylene |
| Order No.  | <a href="#">1719490000</a>  |
| Type       | GWDR PG21-PO  |
| GTIN (EAN) | 4008190352752   |
| Qty.       | 100 items   |

**GWDR PG21-PO**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 3 mm   | Height (inches) | 0.1181 inch |
| Net weight | 0.52 g |                 |             |

**Temperatures**

Operating temperature -30 °C...90 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General information**

|                                   |          |                                   |              |
|-----------------------------------|----------|-----------------------------------|--------------|
| Silicone                          | Yes      | Number of wires                   | 1            |
| O.D.                              | 33.5 mm  | Operating temperature range, max. | 90 °C        |
| Operating temperature range, min. | -30 °C   | Thickness                         | 3.00 mm      |
| Cable gland                       | PG 21    | Basic material                    | Polyethylene |
| Diameter of sealing ring          | 33.50 mm | Sealing                           | PE-HD        |
| External thread                   | PG 21    | Internal thread                   | PG 21        |
| Inside diameter D2                | 28.30 mm |                                   |              |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001181    | ETIM 9.0    | EC001181    |
| ETIM 10.0   | EC001181    | ECLASS 14.0 | 27-43-03-19 |
| ECLASS 15.0 | 27-43-03-19 |             |             |

**Drawings**

