TM 6/12 HF/HB



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com









The TM sleeves contain no halogens and virtually no pollutants. The sleeves are equipped with the TM-I 12 or TM-I 18 tags. They cover a wide range of applications for cables and lines. This system has particularly proved its worth in traffic engineering. The slim design guarantees firm seating on the conductor.

- Halogen-free
- The slim design guarantees firm seating on the conductor
- TMX 18 for mounting with cable-ties (width 3.6 mm)

General ordering data

	'
Version	TM, Socket x 22.2 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.: 15 - 24 mm
Order No.	<u>1719880000</u>
Туре	TM 6/12 HF/HB
GTIN (EAN)	4008190353230
Qty.	200 items



TM 6/12 HF/HB



Weidmüller Interface GmbH & Co. KG

27-28-11-02

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

ROHS	Conform		
Dimensions and weights			
Depth	23.6 mm	Depth (inches)	0.9291 inch
Height	12 mm	Height (inches)	0.4724 inch
Width	22.2 mm	Width (inches)	0.874 inch
Net weight	0.58 g	Trial (menso)	0.07.1
Temperatures			
Operating temperature range	-4080 °C		
Environmental Product Com	pliance		
	•		
RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate 0.003 kg CO2 eq.		
General data			
-		AAC Id	00.0
Type of printing	neutral	Width	22.2 mm
UL 94 flammability rating	HB -40 °C	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C No	Colour Basic material	Transparent
Halogen Recommended industries	Transportation, Machinery	Operating temperature range	Polyethylene LD -4080 °C
	,	Operating temperature range	-4000 C
Conductor and cable marke	rs		
Halogen	No	Conductor cross-section, max.	150 mm²
Conductor cross-section, min.	35 mm ²	Conductor O.D., max.	24 mm
Conductor O.D., min.	15 mm	Conductor O.D.	15 - 24 mm
Cross-section for connected wire	35 - 150 mm²		
Classifications			
ETIM 8.0	EC001530	ETIM 9.0	EC001530

EC001530

27-28-11-02

ETIM 10.0

ECLASS 15.0

ECLASS 14.0