


LM MT300 105/148 SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

General ordering data

Version	LaserMark, Device markers, 148 x 105 mm, silver
Order No.	1724170001
Type	LM MT300 105/148 SI
GTIN (EAN)	4008 190369040
Qty.	10 items

LM MT300 105/148 SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	148 mm	Height (inches)	5.8268 inch
Width	105 mm	Width (inches)	4.1338 inch
Net weight	12.3 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Acrylate adhesive	
Number per sheet	4	
Printing method	Laser print	
Version	Self-adhesive	
Width	105 mm	
UL 94 flammability rating	HB	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Colour	silver	
Halogen	No	
Basic material	Polyester, PVC-free	
Printed characters	without	
Number of markers per packaging unit	40	
Number of markers per packaging unit	Form of supply	Label sheet
	Number of combinations per packaging unit	10
	Number of markers per combination	4
Approval acc. to UL 969	Yes	
Number of markers per combination	1 Label sheet = 4 Device markers	
Operating temperature range	-40...150 °C	

Device markers

Halogen	No
---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings

