


ESG 7/20 SIRIUS MC NE GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ESG, Device markers x 20 mm, PA 66, Colour: yellow, pluggable
Order No.	1736181687
Type	ESG 7/20 SIRIUS MC NE GE
GTIN (EAN)	4032248208265
Qty.	200 items

ESG 7/20 SIRIUS MC NE GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	7 mm	Height (inches)	0.2756 inch
Width	20 mm	Width (inches)	0.7874 inch
Net weight	0.51 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.003 kg CO2 eq.

General data

Material colour according to resistance code	4	
Number per sheet	40	
Version	pluggable	
Width	20 mm	
UL 94 flammability rating	V-2	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Colour	yellow	
Halogen	No	
Basic material	PA 66	
Printed characters	without	
Number of markers per packaging unit	Form of supply	MultiCard
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2	
Number of markers per combination	1 MultiCard = Device markers	
Operating temperature range	-40...100 °C	
Application/manufacturer	Siemens Sirius 3R	

Device markers

Halogen	No
---------	----

Classifications


ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

ESG 7/20 SIRIUS MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



ESG 7/20 SIRIUS MC NE GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Accessories



General ordering data

Type	SCHS3 K	Version	
Order No.	1753480000	Device markers, Accessories x 10 mm, PVC, Colour: black, Self-adhesive	
GTIN (EAN)	4032248014347		
Qty.	50 ST		
Type	SCHS4 K	Version	
Order No.	1753460000	Device markers, Accessories x 10 mm, PVC, Colour: grey, Self-adhesive	
GTIN (EAN)	4032248014323		
Qty.	50 ST		

WKM for inlay tags



The halogen-free, transparent pocket of the WKM offers outstanding protection against environmental influences. Thanks to firm fixation with cable ties, it is suitable for almost all wire cross-sections.

The pre-printed tags are simply inserted into the WKM holder and secured with a clip. WKM cable markers are the right solution for maximum efficiency in on-site marking. Your advantage when using WKM cables

- Paper and polyester labels can be printed individually with conventional office printers
- The robust design in combination with MultiCard ELS tags guarantees maximum protection against environmental influences

General ordering data

Type	WKM 8/20	Version	
Order No.	1753490000	WKM, Conductor and cable markers, 7 - 115 mm, 20 x 8 mm, Wire and cable markers, Transparent	
GTIN (EAN)	4032248010615		
Qty.	50 ST		