

GWDR M16-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Version	GWDR NP (flat gasket - neoprene), Sealing ring, M 16, Neoprene
Order No.	1736230000
Type	GWDR M16-NP
GTIN (EAN)	4008 190956028
Qty.	50 items

GWDR M16-NP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	1.2 mm	Height (inches)	0.0472 inch
Net weight	0.4 g		

Temperatures

Operating temperature -40 °C... 100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Silicone	No	Number of wires	1
O.D.	22 mm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	Yes	Thickness	1.20 mm
Cable gland	M 16	Basic material	Neoprene
Diameter of sealing ring	22.00 mm	Sealing	Neoprene
External thread	M 16	Internal thread	M 16
Inside diameter D2	16.00 mm		

Technical data

Colour Deep black

Classifications

ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

Drawings

