


## VT SF 4/12 MC NE WS V0

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

#### Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

#### General ordering data

Version	SlimFix, Conductor and cable markers, 3.6 - 6 mm, 12 x 5.7 mm, white
Order No.	<a href="#">1746030001</a>
Type	VT SF 4/12 MC NE WS V0
GTIN (EAN)	4008190986353
Qty.	192 items

## VT SF 4/12 MC NE WS V0

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	6.1 mm	Depth (inches)	0.2402 inch
Height	12 mm	Height (inches)	0.4724 inch
Width	5.7 mm	Width (inches)	0.2244 inch
Net weight	0.36 g		

### Temperatures

Operating temperature range	-50...120 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.004 kg CO2 eq.

### General data

Material colour according to resistance code	9	
Type of printing	neutral	
Width	5.7 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	120 °C	
Operating temperature range, min.	-50 °C	
Colour	white	
Halogen	No	
Basic material	Polyamide 66	
Number of markers per packaging unit	Form of supply	MultiCard
Size of labelling field	12 x 5.7 mm	
Recommended industries compatible printer	Transportation, Machinery <a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a>	
Number of markers per combination	1 MultiCard = Conductor and cable markers	
Operating temperature range	-50...120 °C	

### Conductor and cable markers

Halogen	No	Conductor cross-section, max.	4 mm <sup>2</sup>
Conductor cross-section, min.	2.5 mm <sup>2</sup>	Conductor O.D., max.	6 mm
Conductor O.D., min.	3.6 mm	Conductor O.D.	3.6 - 6 mm
Cross-section for connected wire	2.5 - 4 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**

