

VT SF 4.5/21 MC NE RT V0


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Version	SlimFix, Conductor and cable markers, 4.1 - 4.9 mm, 21 x 7.4 mm, red
Order No.	1730570003
Type	VT SF 4.5/21 MC NE RT V0
GTIN (EAN)	4008190954581
Qty.	192 items

VT SF 4.5/21 MC NE RT V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	6.5 mm	Depth (inches)	0.2559 inch
Height	21 mm	Height (inches)	0.8268 inch
Width	7.4 mm	Width (inches)	0.2913 inch
Net weight	0.82 g		

Temperatures

Operating temperature range	-50...120 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.005 kg CO2 eq.	

General data

Type of printing	neutral		
Width	7.4 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	120 °C		
Operating temperature range, min.	-50 °C		
Colour	red		
Halogen	No		
Basic material	Polyamide 66		
Number of markers per packaging unit	Form of supply	MultiCard	
Size of labelling field	21 x 7.4 mm		
Recommended industries	Transportation, Machinery		
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2		
Number of markers per combination	1 MultiCard = Conductor and cable markers		
Operating temperature range	-50...120 °C		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	6 mm ²
Conductor cross-section, min.	4 mm ²	Conductor O.D., max.	4.9 mm
Conductor O.D., min.	4.1 mm	Conductor O.D.	4.1 - 4.9 mm
Cross-section for connected wire	4 - 6 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

VT SF 4.5/21 MC NE RT V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

