

VT SF 0/12 MC NE WS V0


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

| | |
|------------|--|
| Version | SlimFix, Conductor and cable markers, 1.2 - 1.6 mm, 12 x 3.2 mm, white |
| Order No. | 1752110001 |
| Type | VT SF 0/12 MC NE WS V0 |
| GTIN (EAN) | 4032248002917 |
| Qty. | 800 items |

VT SF 0/12 MC NE WS V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 3.2 mm | Depth (inches) | 0.126 inch |
| Height | 12 mm | Height (inches) | 0.4724 inch |
| Width | 3.2 mm | Width (inches) | 0.126 inch |
| Net weight | 0.2 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -50...120 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | | |
|--------------------------|-----------------------------|------------------|
| RoHS Compliance Status | Compliant without exemption | |
| REACH SVHC | No SVHC above 0.1 wt% | |
| Product Carbon Footprint | Cradle to gate | 0.002 kg CO2 eq. |

General data

| | | |
|--|--|-----------|
| Material colour according to resistance code | 9 | |
| Type of printing | neutral | |
| Width | 3.2 mm | |
| UL 94 flammability rating | V-0 | |
| Operating temperature range, max. | 120 °C | |
| Operating temperature range, min. | -50 °C | |
| Colour | white | |
| Halogen | No | |
| Basic material | Polyamide 66 | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Size of labelling field | 12 x 3.2 mm | |
| Recommended industries compatible printer | Transportation, Machinery PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2 | |
| Number of markers per combination | 1 MultiCard = Conductor and cable markers | |
| Operating temperature range | -50...120 °C | |

Conductor and cable markers

| | | | |
|----------------------------------|----------------------------|-------------------------------|---------------------|
| Halogen | No | Conductor cross-section, max. | 0.5 mm ² |
| Conductor cross-section, min. | 0.25 mm ² | Conductor O.D., max. | 1.6 mm |
| Conductor O.D., min. | 1.2 mm | Conductor O.D. | 1.2 - 1.6 mm |
| Cross-section for connected wire | 0.25 - 0.5 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

Drawings

