



**LP 5.08/08/135 3.2SN OR BX****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

Similar to illustration

Test point, 32 A and 6 mm<sup>2</sup> conductor cross-section are feasible with this PCB terminal with proven clamping yoke connection at 5.00 and 5.08 mm pitch, conductor outlet direction 90° and 135°, with extensive auxiliary functions.

**General ordering data**

|              |                                                                                                                                                                                             |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version      | Printed circuit board terminals, 5.08 mm, Number of poles: 8, 135°, Solder pin length (l): 3.2 mm, tinned, orange, Clamping yoke connection, Clamping range, max. : 6 mm <sup>2</sup> , Box |
| Order No.    | <a href="#">1752940000</a>                                                                                                                                                                  |
| Type         | LP 5.08/08/135 3.2SN OR BX                                                                                                                                                                  |
| GTIN (EAN)   | 4032248052837                                                                                                                                                                               |
| Qty.         | 50 items                                                                                                                                                                                    |
| Product data | IEC: 500 V / 32 A / 0.5 - 6 mm <sup>2</sup><br>UL: 300 V / 20 A / AWG 26 - AWG 12                                                                                                           |
| Packaging    | Box                                                                                                                                                                                         |

## LP 5.08/08/135 3.2SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

|                          |             |                 |             |
|--------------------------|-------------|-----------------|-------------|
| Depth                    | 17.5 mm     | Depth (inches)  | 0.689 inch  |
| Height                   | 20 mm       | Height (inches) | 0.7874 inch |
| Height of lowest version | 16.8 mm     | Width           | 41.24 mm    |
| Width (inches)           | 1.6236 inch | Net weight      | 12.56 g     |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## System parameters

|                                                   |                             |                                              |                          |
|---------------------------------------------------|-----------------------------|----------------------------------------------|--------------------------|
| Product family                                    | OMNIMATE Signal - series LP | Wire connection method                       | Clamping yoke connection |
| Mounting onto the PCB                             | THT solder connection       | Conductor outlet direction                   | 135°                     |
| Pitch in mm (P)                                   | 5.08 mm                     | Pitch in inches (P)                          | 0.200 "                  |
| Number of poles                                   | 8                           | Pin series quantity                          | 1                        |
| Fitted by customer                                | Yes                         | Number of rows                               | 1                        |
| Max. adjacent poles per row                       | 24                          | Solder pin length (l)                        | 3.2 mm                   |
| Solder pin dimensions                             | 0.75 x 0.9 mm               | Solder eyelet hole diameter (D)              | 1.3 mm                   |
| Solder eyelet hole diameter tolerance (D)+ 0,1 mm |                             | Number of solder pins per pole               | 1                        |
| Screwdriver blade                                 | 0.6 x 3.5                   | Screwdriver blade standard                   | DIN 5264                 |
| Tightening torque, min.                           | 0.5 Nm                      | Tightening torque, max.                      | 0.6 Nm                   |
| Clamping screw                                    | M 3                         | Stripping length                             | 6 mm                     |
| L1 in mm                                          | 35.56 mm                    | L1 in inches                                 | 1.400 "                  |
| Touch-safe protection acc. to DIN VDE 0470        | IP 20                       | Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch   |
| Protection degree                                 | IP20                        | Volume resistance                            | 1.20 mΩ                  |

## Material data

|                                       |          |                                       |                           |
|---------------------------------------|----------|---------------------------------------|---------------------------|
| Insulating material                   | PA       | Colour                                | orange                    |
| Colour chart (similar)                | RAL 2000 | Insulating material group             | I                         |
| Comparative Tracking Index (CTI)      | ≥ 600    | Moisture Level (MSL)                  |                           |
| UL 94 flammability rating             | V-2      | Contact material                      | Cu-alloy                  |
| Contact surface                       | tinned   | Coating                               | 1-3 µm Ni, 4-6 µm SN      |
| Tinning type                          | matt     | Layer structure of solder connection  | 4...6 µm Ni / 4...6 µm Sn |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C                     |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 100 °C                    |
| Temperature range, installation, min. | -25 °C   | Temperature range, installation, max. | 100 °C                    |

## Conductors suitable for connection

|                                         |                      |
|-----------------------------------------|----------------------|
| Clamping range, min.                    | 0.13 mm <sup>2</sup> |
| Clamping range, max.                    | 6 mm <sup>2</sup>    |
| Wire connection cross section AWG, min. | AWG 26               |

## LP 5.08/08/135 3.2SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

|                                                         |                                        |                                                                                                                                                                        |                              |                            |      |  |
|---------------------------------------------------------|----------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------|----------------------------|------|--|
| Wire connection cross section AWG, max.                 | AWG 12                                 |                                                                                                                                                                        |                              |                            |      |  |
| Solid, min. H05(07) V-U                                 | 0.5 mm²                                |                                                                                                                                                                        |                              |                            |      |  |
| Solid, max. H05(07) V-U                                 | 6 mm²                                  |                                                                                                                                                                        |                              |                            |      |  |
| Flexible, min. H05(07) V-K                              | 0.5 mm²                                |                                                                                                                                                                        |                              |                            |      |  |
| Flexible, max. H05(07) V-K                              | 4 mm²                                  |                                                                                                                                                                        |                              |                            |      |  |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.5 mm² min. |                                        |                                                                                                                                                                        |                              |                            |      |  |
| w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm² max. |                                        |                                                                                                                                                                        |                              |                            |      |  |
| w. wire end ferrule, DIN 46228 pt 1, min.               | 0.5 mm²                                |                                                                                                                                                                        |                              |                            |      |  |
| w. wire end ferrule, DIN 46228 pt 1, max.               | 2.5 mm²                                |                                                                                                                                                                        |                              |                            |      |  |
| Plug gauge in accordance with EN 60999 a x b; ø         | 2.8 mm x 2.4 mm; 3.0 mm                |                                                                                                                                                                        |                              |                            |      |  |
| Clampable conductor                                     | Cross-section for conductor connection | Type                                                                                                                                                                   | fine-wired                   |                            |      |  |
|                                                         |                                        | nominal                                                                                                                                                                | 0.5 mm²                      |                            |      |  |
|                                                         |                                        | Stripping length                                                                                                                                                       | nominal                      | 8 mm                       |      |  |
|                                                         |                                        | Recommended wire-end ferrule                                                                                                                                           | <a href="#">H0.5/12 OR</a>   |                            |      |  |
|                                                         |                                        | Stripping length                                                                                                                                                       | nominal                      | 6 mm                       |      |  |
|                                                         | wire end ferrule                       | Recommended wire-end ferrule                                                                                                                                           | <a href="#">H0.5/6</a>       |                            |      |  |
|                                                         |                                        | Cross-section for conductor connection                                                                                                                                 | Type                         | fine-wired                 |      |  |
|                                                         |                                        |                                                                                                                                                                        | nominal                      | 0.75 mm²                   |      |  |
|                                                         |                                        |                                                                                                                                                                        | Stripping length             | nominal                    | 8 mm |  |
|                                                         |                                        |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H0.75/12 W</a> |      |  |
|                                                         | Stripping length                       |                                                                                                                                                                        | nominal                      | 6 mm                       |      |  |
|                                                         | wire end ferrule                       | Recommended wire-end ferrule                                                                                                                                           | <a href="#">H0.75/6</a>      |                            |      |  |
|                                                         |                                        | Cross-section for conductor connection                                                                                                                                 | Type                         | fine-wired                 |      |  |
|                                                         |                                        |                                                                                                                                                                        | nominal                      | 1 mm²                      |      |  |
|                                                         |                                        |                                                                                                                                                                        | Stripping length             | nominal                    | 8 mm |  |
|                                                         |                                        |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H1.0/12 GE</a> |      |  |
|                                                         | Stripping length                       |                                                                                                                                                                        | nominal                      | 6 mm                       |      |  |
|                                                         | wire end ferrule                       | Recommended wire-end ferrule                                                                                                                                           | <a href="#">H1.0/6</a>       |                            |      |  |
| Reference text                                          |                                        | Length of ferrules is to be chosen depending on the product and the rated voltage., The outside diameter of the plastic collar should not be larger than the pitch (P) |                              |                            |      |  |

## Rated data acc. to IEC

|                                                                           |                        |                                                                       |                   |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 32 A              |
| Rated current, max. number of poles (Tu=20°C)                             | 30.5 A                 | Rated current, min. number of poles (Tu=40°C)                         | 32 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 25 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 500 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 250 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 250 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV                   | Short-time withstand current resistance                               | 3 x 1s with 120 A |

## LP 5.08/08/135 3.2SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rated data acc. to CSA

|                                   |                                                                        |                                   |                |
|-----------------------------------|------------------------------------------------------------------------|-----------------------------------|----------------|
| Institute (CSA)                   | CSA                                                                    | Certificate No. (CSA)             | 200039-1202191 |
| Rated voltage (Use group B / CSA) | 300 V                                                                  | Rated voltage (Use group D / CSA) | 300 V          |
| Rated current (Use group B / CSA) | 20 A                                                                   | Rated current (Use group D / CSA) | 10 A           |
| Wire cross-section, AWG, min.     | AWG 26                                                                 | Wire cross-section, AWG, max.     | AWG 12         |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |                                   |                |

## Rated data acc. to UL 1059

|                                       |        |                                       |        |
|---------------------------------------|--------|---------------------------------------|--------|
| Rated voltage (Use group B / UL 1059) | 300 V  | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 20 A   | Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 26 | Wire cross-section, AWG, max.         | AWG 12 |

## Packing

|           |           |            |           |
|-----------|-----------|------------|-----------|
| Packaging | Box       | VPE length | 155.00 mm |
| VPE width | 100.00 mm | VPE height | 50.00 mm  |


## Important note

|                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |  |  |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                                                                                                                                                                                                                                                                                                                                                            |  |  |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Wire end ferrule without plastic collar to DIN 46228/1</li> <li>• Wire end ferrule with plastic collar to DIN 46228/4</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• The test point can only be used as potential-pickup point.</li> <li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |  |  |


## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002643    | ETIM 9.0    | EC002643    |
| ETIM 10.0   | EC002643    | ECLASS 14.0 | 27-46-01-01 |
| ECLASS 15.0 | 27-46-01-01 |             |             |

## Dimensional drawing



## Graph



## LP 5.08/08/135 3.2SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Intermediate plates



The maximum voltage is based on the minimum distance. Intermediate plates increase the creepage and clearance distances between different potentials and permit higher rated voltages or a clear separation, e.g. between mains and low voltages or different protection zones.

The dovetail joint enables easy installation and guarantees a secure fit. Other characteristics include:

- Pitch extended by 1.27 or 2.54mm - all other combinations possible
- Colour coding ensures visual differentiation
- Different geometries for standard designs.

Incomplete individual assemblies avoided because separate terminal blocks combine to form a single holistic unit. Ready-assembled on request.

The advantages: efficient processing, increased stability, improved reliability.

## General ordering data

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | LPZP 2.54/135 OR           | Version                                                           |
| Order No.  | <a href="#">1753740000</a> | Printed circuit board terminals, Accessories, Intermediate plate, |
| GTIN (EAN) | 4032248058648              | orange, Number of poles: 1                                        |
| Qty.       | 100 ST                     |                                                                   |

## Additional accessories



No task is too small when creating the perfect solution. Connections form just one part of the overall process.

Small details are often the key to the perfect solution in applications where potentials are tested, grouped or even isolated.


A system is not a system without small but essential details:

- Test plugs ensure reliable pick-up from diagnostic sockets

In tandem with the manufacturing process and application.

## General ordering data

|            |                            |                                                                      |
|------------|----------------------------|----------------------------------------------------------------------|
| Type       | PS 2.0 MC                  | Version                                                              |
| Order No.  | <a href="#">0310000000</a> | PCB plug-in connector, Accessories, Test plug, red, Number of poles: |
| GTIN (EAN) | 4008190000059              | 1                                                                    |
| Qty.       | 20 ST                      |                                                                      |

**Accessories****Cross-connections**

Large potential for small terminals.

For efficient electrical distribution directly at the connection:

- Isolated comb rail
- Available with the most standard pole numbers
- Easy to shorten

Simply reduce in size to match the number of poles and connect with the conductor in a single working procedure.

For retrofitting or deliberate reduction of the thermal load on the PCB.

**General ordering data**

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | LPA QB 2                   | Version                                                               |
| Order No.  | <a href="#">1472200000</a> | Printed circuit board terminals, Accessories, Cross-connector, Number |
| GTIN (EAN) | 4008190096298              | of poles: 2                                                           |
| Qty.       | 50 ST                      |                                                                       |
| Type       | LPA QB 3                   | Version                                                               |
| Order No.  | <a href="#">1472300000</a> | Printed circuit board terminals, Accessories, Cross-connector, Number |
| GTIN (EAN) | 4008190093914              | of poles: 3                                                           |
| Qty.       | 50 ST                      |                                                                       |
| Type       | LPA QB 4                   | Version                                                               |
| Order No.  | <a href="#">1472400000</a> | Printed circuit board terminals, Accessories, Cross-connector, Number |
| GTIN (EAN) | 4008190053918              | of poles: 4                                                           |
| Qty.       | 50 ST                      |                                                                       |