

**ZQV 10/2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Accessories, Cross-connector, 57 A
Order No.	<a href="#">1739680000</a>
Type	ZQV 10/2
GTIN (EAN)	4008190957131
Qty.	25 items

**Technical data****Approvals**

RoHS	Conform
------	---------

**Dimensions and weights**

Depth	35.1 mm	Depth (inches)	1.3819 inch
Height	17.8 mm	Height (inches)	0.7008 inch
Width	4 mm	Width (inches)	0.1575 inch
Net weight	5.9 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-60 °C...85 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

**System specifications**

Version	For the terminals
---------	-------------------

**Additional technical data**

Type of fixing	Plugged	Installation advice	Direct mounting
Explosion-tested version	Yes		

**Dimensions**

Pitch in mm (P)	10.00 mm
-----------------	----------

**General**

Number of poles	2	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

**Rating data**

Rated voltage	400 V	Nominal current	57 A
---------------	-------	-----------------	------

**Important note**

Product information	Due to stability and temperature reasons it is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400V. The voltage is reduced to 25V if cut cross connection with blank cut edges are used. Cross connections with >10 poles have bare cut edges ex works.
---------------------	---

**Technical data****Classifications**

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		