


## SYMBOL-P. 75X75X75 B/DR

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

Symbol Pack is a bag with pre-printed electrical symbols on perforated sheets. The on-site solution for labelling electrical systems; highly resistant to alkyl alcohols and benzenes.

### General ordering data

Version	Device markers, Device markers, 75 x 75 mm, yellow
Order No.	<a href="#">1741110000</a>
Type	SYMBOL-P. 75X75X75 B/DR
GTIN (EAN)	4008 190964337
Qty.	1 items

## SYMBOL-P. 75X75X75 B/DR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	75 mm	Height (inches)	2.9527 inch
Width	75 mm	Width (inches)	2.9527 inch
Net weight	10 g		

### Temperatures

Operating temperature range	-45...80 °C
-----------------------------	-------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Adhesive	Permanent acrylic copolymer		
Material colour according to resistance code	4		
Number per sheet	2		
Version	Self-adhesive		
Width	75 mm		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-45 °C		
Colour	yellow		
Basic material	Acrylic-coated fibre webbing		
Colour of printing	black		
Printed characters	Mixed characters		
Number of markers per packaging unit	20		
Number of markers per packaging unit	Form of supply	Label sheet	
	Number of combinations per packaging unit	10	
	Number of markers per combination	2	
Number of markers per combination	1 Label sheet = 2 Device markers		
Operating temperature range	-45...80 °C		
Imprint	Lightning flash in triangle		

### Important note

Product information	Delivery unit: 10 sheets = 20 labels
---------------------	--------------------------------------

### Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		