

HDC CM 3 MC



The module is assembled with HE crimp contacts. The crimp contact features a stainless steel spring. The provides a secure snap-in contact with the module. A customized contact removal tool is available for removing the contacts. The power modules can be ordered with or without the integrated module release aid. A removal tool is available for modules that do not have the integrated module release aid.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	1758360000
Type	HDC CM 3 MC
GTIN (EAN)	4032248019588
Qty.	10 items

HDC CM 3 MC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	34 mm	Depth (inches)	1.3386 inch
Height	31.4 mm	Height (inches)	1.2362 inch
Width	11.4 mm	Width (inches)	0.4488 inch
Net weight	6.8 g		

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

ConCept Pneumatic module

UL 94 flammability rating V-0 Colour beige

Dimensions

Width 11.4 mm Total length base 34 mm
Height of plug 31.4 mm

General data

Number of poles	3	Type of connection	Crimp connection
UL 94 flammability rating	V-0	Volume resistance	≤1 mΩ
Colour	beige	Insulation resistance	1012 Ω
Type	Pin	Surge voltage category	III
Pollution severity	3	Basic material	Polycarbonate, glass fibre reinforced
Series	ConCept module	Rated voltage (DIN EN 61984)	690 V
Rated impulse voltage (DIN EN 61984)	8 kV	Rated current (DIN EN 61984)	40 A
Free from halogens	false	Low smoke acc. DIN EN 45545-2	Yes

Connection data PE

Connection type PE Screw connection via module frame

Version


Wire connection cross section AWG, max.	AWG 7	Stripping length, rated connection	10 mm
Type of connection	Crimp connection	Volume resistance	≤1 mΩ
Wire connection cross section AWG, min.	AWG 16	Conductor cross-section, max.	10 mm ²
Conductor cross-section, min.	1.5 mm ²	Basic material	Polycarbonate, glass fibre reinforced

Technical data

Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-05
ECLASS 15.0	27-44-02-05		

Drawings



HDC CM 3 MC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Modul removal tool



Weidmüller offers a variety of crimping tools, no-contact tools, and fibre optic tools.

General ordering data

Type	HDC-DW-MOD	Version	
Order No.	1688200000	Tool miscellaneous, Contact Removal Tool	
GTIN (EAN)	4008190857189		
Qty.	1 ST		

Crimping tools



Crimping tools for turned contacts

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

Type	CTX CM 1.6/2.5	Version	
Order No.	9018490000	Pressing tool, Crimping tool for contacts, 0.14mm ² , 4mm ² , W crimp	
GTIN (EAN)	4008190884598		
Qty.	1 ST		
Type	CTX CM 3.6	Version	
Order No.	9018480000	Pressing tool, Crimping tool for contacts, 4mm ² , 10mm ² , W crimp	
GTIN (EAN)	4008190884581		
Qty.	1 ST		

Contact removal tools



Weidmüller offers a variety of crimping tools, contact removal tools, and fibre optic tools.

HDC CM 3 MC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

Type	REMOVAL TOOL CM 3	Version	
Order No.	1866710000	Tools, Contact Removal Tool	
GTIN (EAN)	4032248437030		
Qty.	1 ST		

Crimp contacts CM3



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Type	HDC-C-M3-SM1.5AG	Version	
Order No.	1698120000	Heavy-duty connectors, Crimp contact, CM 3, Male, Conductor cross-section, max.: 1.5, turned, Copper alloy	
GTIN (EAN)	4008190885038		
Qty.	100 ST		
Type	HDC-C-M3-SM2.5AG	Version	
Order No.	1698140000	Heavy-duty connectors, Crimp contact, CM 3, Male, Conductor cross-section, max.: 2.5, turned, Copper alloy	
GTIN (EAN)	4008190885052		
Qty.	100 ST		
Type	HDC-C-M3-SM4.0AG	Version	
Order No.	1682260000	Heavy-duty connectors, Crimp contact, CM 3, Male, Conductor cross-section, max.: 4, turned, Copper alloy	
GTIN (EAN)	4008190473990		
Qty.	100 ST		
Type	HDC-C-M3-SM6.0AG	Version	
Order No.	1682280000	Heavy-duty connectors, Crimp contact, CM 3, Male, Conductor cross-section, max.: 6, turned, Copper alloy	
GTIN (EAN)	4008190474010		
Qty.	100 ST		
Type	HDC-C-M3-SM10.0AG	Version	
Order No.	1682300000	Heavy-duty connectors, Crimp contact, CM 3, Male, Conductor cross-section, max.: 10, turned, Copper alloy	
GTIN (EAN)	4008190474034		
Qty.	100 ST		