


**VT SF 00/12 MC NE WS V0**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

**Advantages:**

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

**General ordering data**

|            |  |
|------------|--|
| Version    | SlimFix, Conductor and cable markers, 1 - 1.3 mm, 12 x 3.2 mm, white |
| Order No.  | <a href="#">1752200001</a>   |
| Type       | VT SF 00/12 MC NE WS V0  |
| GTIN (EAN) | 4032248003624  |
| Qty.       | 800 items  |

Technical data

Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 3.2 mm | Depth (inches)  | 0.126 inch  |
| Height     | 12 mm  | Height (inches) | 0.4724 inch |
| Width      | 3.2 mm | Width (inches)  | 0.126 inch  |
| Net weight | 0.23 g |                 |             |

Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -50...120 °C |
|-----------------------------|--------------|

Environmental Product Compliance

|                          |                             |                  |  |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                  |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |  |
| Product Carbon Footprint | Cradle to gate              | 0.002 kg CO2 eq. |  |

General data

|  |  |           |  |
|--|--|-----------|--|
| Material colour according to resistance code | 9  |           |  |
| Type of printing                             | neutral  |           |  |
| Width  | 3.2 mm   |           |  |
| UL 94 flammability rating                    | V-0  |           |  |
| Operating temperature range, max.            | 120 °C   |           |  |
| Operating temperature range, min.            | -50 °C   |           |  |
| Colour                                       | white  |           |  |
| Halogen                                      | No   |           |  |
| Basic material                               | Polyamide 66   |           |  |
| Number of markers per packaging unit         | Form of supply   | MultiCard |  |
| Size of labelling field                      | 12 x 3.2 mm  |           |  |
| Recommended industries compatible printer    | Transportation, Machinery<br><a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a> |           |  |
| Number of markers per combination            | 1 MultiCard = Conductor and cable markers  |           |  |
| Operating temperature range                  | -50...120 °C   |           |  |

Conductor and cable markers

|                                  |                             |                               |                      |
|----------------------------------|-----------------------------|-------------------------------|----------------------|
| Halogen                          | No                          | Conductor cross-section, max. | 0.25 mm <sup>2</sup> |
| Conductor cross-section, min.    | 0.18 mm <sup>2</sup>        | Conductor O.D., max.          | 1.3 mm               |
| Conductor O.D., min.             | 1 mm                        | Conductor O.D.                | 1 - 1.3 mm           |
| Cross-section for connected wire | 0.18 - 0.25 mm <sup>2</sup> |                               |                      |

Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**

