


**VT SF 00/12 MC NE GE V0**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)


Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

**General ordering data**

Version	SlimFix, Conductor and cable markers, 1 - 1.3 mm, 12 x 3.2 mm, yellow
Order No.	<a href="#">1752200004</a>
Type	VT SF 00/12 MC NE GE V0
GTIN (EAN)	4032248003655
Qty.	800 items

**VT SF 00/12 MC NE GE V0**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	3.2 mm	Depth (inches)	0.126 inch
Height	12 mm	Height (inches)	0.4724 inch
Width	3.2 mm	Width (inches)	0.126 inch
Net weight	0.16 g		

**Temperatures**

Operating temperature range -50...120 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.002 kg CO2 eq.	

**General data**

Material colour according to resistance code	4		
Type of printing	neutral		
Width	3.2 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	120 °C		
Operating temperature range, min.	-50 °C		
Colour	yellow		
Halogen	No		
Basic material	Polyamide 66		
Number of markers per packaging unit	Form of supply	MultiCard	
Size of labelling field	12 x 3.2 mm		
Recommended industries compatible printer	Transportation, Machinery <a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a>		
Number of markers per combination	1 MultiCard = Conductor and cable markers		
Operating temperature range	-50...120 °C		

**Conductor and cable markers**

Halogen	No	Conductor cross-section, max.	0.25 mm <sup>2</sup>
Conductor cross-section, min.	0.18 mm <sup>2</sup>	Conductor O.D., max.	1.3 mm
Conductor O.D., min.	1 mm	Conductor O.D.	1 - 1.3 mm
Cross-section for connected wire	0.18 - 0.25 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**

