

CLI TM 20-66**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections. Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

Version	CableLine, Conductor and cable markers, 10 - 317 mm, 66 x 11.3 mm, Transparent
Order No.	1763390000
Type	CLI TM 20-66
GTIN (EAN)	4032248050840
Qty.	50 items

CLI TM 20-66

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	66 mm	Height (inches)	2.5984 inch
Width	11.3 mm	Width (inches)	0.4449 inch
Net weight	1.3 g		

Temperatures

Operating temperature range	-30...60 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	
Width	11.3 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	60 °C	
Operating temperature range, min.	-30 °C	
Colour	Transparent	
Halogen	Yes	
Basic material	PVC	
Number of markers per packaging unit	Form of supply	Component part
Recommended industries	Process, Machinery	
Number of markers per combination	1 Component part = Conductor and cable markers	
Operating temperature range	-30...60 °C	

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	500 mm ²
Conductor cross-section, min.	16 mm ²	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor O.D.	10 - 317 mm
Cross-section for connected wire	16 - 500 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

CLI TM 20-66

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 9/17 K MC NE WS	Version
Order No.	1674760000	ESG, Device markers x 17 mm, PA 66, Colour: white, Self-adhesive
GTIN (EAN)	4008190447649	
Qty.	200 ST	

CLI F 2-17,5



The Weidmüller range of conductor and cable marker products provides users with solutions for a wide variety of applications. The field of application ranges from thin conductors to cables with large outside diameters. The product range includes combination systems with individual tags, transparent sleeves and markers which can be fastened with cable ties. Open and closed markers, as well as printed or blank markers for individual labelling are available. Weidmüller's halogen-free and low-emission conductor markers are in compliance with European standards as well as with the in-house standards of well-known plant manufacturers. Markers for conductors and cables - Systems are available for:

- Clipping on pre-printed markers to suit individual labelling requirements
- Labelling with characters from a standard character set
- Combining individual, pre-printed characters to form a character code
- Customer labelling with SMark laser, PrintJet, MCP Plus plotter, MC-Mobil, laser printer (DIN A4 format), thermal transfer printer or STI pen

A selection of samples can be found in the Weidmüller conductor marker sample bag, order No. 1640420000.

General ordering data

Type	CLI F 2-17,5 WS/GE	Version
Order No.	1764050000	CableLine, Conductor and cable markers, 10 - 317 mm, 17.5 x 9 mm,
GTIN (EAN)	4032248052431	white
Qty.	10 ST	

Accessorieswww.weidmueller.com**ESO insert tags****General ordering data**

Type	ESO 5 S DIN A4 WS	Version
Order No.	1631920000	Terminal markers, Insert markers, 40 x 7 mm, white
GTIN (EAN)	4008190206673	
Qty.	10 ST	