



CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections. Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 10 - 317 mm, 66 x 11.3 mm, Transparent |
| Order No. | 1763390000 |
| Type | CLI TM 20-66 |
| GTIN (EAN) | 4032248050840 |
| Qty. | 50 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 5 mm | Depth (inches) | 0.1968 inch |
| Height | 66 mm | Height (inches) | 2.5984 inch |
| Width | 11.3 mm | Width (inches) | 0.4449 inch |
| Net weight | 1.3 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...60 °C |
|-----------------------------|-------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | |
|--------------------------------------|--|----------------|
| Type of printing | neutral | |
| Width | 11.3 mm | |
| UL 94 flammability rating | V-0 | |
| Operating temperature range, max. | 60 °C | |
| Operating temperature range, min. | -30 °C | |
| Colour | Transparent | |
| Halogen | Yes | |
| Basic material | PVC | |
| Number of markers per packaging unit | Form of supply | Component part |
| Recommended industries | Process, Machinery | |
| Number of markers per combination | 1 Component part = Conductor and cable markers | |
| Operating temperature range | -30...60 °C | |

Conductor and cable markers

| | | | |
|----------------------------------|--------------------------|-------------------------------|---------------------|
| Halogen | Yes | Conductor cross-section, max. | 500 mm ² |
| Conductor cross-section, min. | 16 mm ² | Conductor O.D., max. | 317 mm |
| Conductor O.D., min. | 10 mm | Conductor O.D. | 10 - 317 mm |
| Cross-section for connected wire | 16 - 500 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

CLI TM 20-66

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | ESG 9/17 K MC NE WS | Version | |
| Order No. | 1674760000 | ESG, Device markers x 17 mm, PA 66, Colour: white, Self-adhesive | |
| GTIN (EAN) | 4008190447649 | | |
| Qty. | 200 ST | | |

CLI F 2-17,5



The Weidmüller range of conductor and cable marker products provides users with solutions for a wide variety of applications. The field of application ranges from thin conductors to cables with large outside diameters. The product range includes combination systems with individual tags, transparent sleeves and markers which can be fastened with cable ties. Open and closed markers, as well as printed or blank markers for individual labelling are available. Weidmüller's halogen-free and low-emission conductor markers are in compliance with European standards as well as with the in-house standards of well-known plant manufacturers. Markers for conductors and cables - Systems are available for:

- Clipping on pre-printed markers to suit individual labelling requirements
- Labelling with characters from a standard character set
- Combining individual, pre-printed characters to form a character code
- Customer labelling with SMark laser, PrintJet, MCP Plus plotter, MC-Mobilo, laser printer (DIN A4 format), thermal transfer printer or STI pen

A selection of samples can be found in the Weidmüller conductor marker sample bag, order No. 1640420000.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | CLI F 2-17.5 WS/GE | Version | |
| Order No. | 1764050000 | CableLine, Conductor and cable markers, 10 - 317 mm, 17.5 x 9 mm, | |
| GTIN (EAN) | 4032248052431 | white | |
| Qty. | 10 ST | | |

Accessories

ESO insert tags



General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | ESO 5 S DIN A4 WS | Version | |
| Order No. | 1631920000 | Terminal markers, Insert markers, 40 x 7 mm, white | |
| GTIN (EAN) | 4008190206673 | | |
| Qty. | 10 ST | | |