

THM MT30X 15/6 GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

Version	THM, Device markers, 6 x 15 mm, yellow
Order No.	1753231687
Type	THM MT30X 15/6 GE
GTIN (EAN)	4032248008414
Qty.	1 items

THM MT30X 15/6 GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	15 mm	Width (inches)	0.5906 inch
Net weight	208 g		

Temperatures

Operating temperature range -40...150 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Acrylate
Printing method	Thermal transfer
Version	Self-adhesive, halogen-free
Width	15 mm
UL 94 flammability rating	V-0
Operating temperature range, max.	150 °C
Operating temperature range, min.	-40 °C
Colour	yellow
Halogen	No
Basic material	Polyester
Printed characters	without
Number of markers per packaging unit	Form of supply Label reel
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS
Number of markers per combination	1 Label reel = Device markers
Operating temperature range	-40...150 °C
Number per roll	10000

Device markers

Halogen No

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings

