

## ZQV 1.5N/R3.5/3 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### General ordering data

Version	Accessories, Cross-connector, 17.5 A
Order No.	<a href="#">1754220000</a>
Type	ZQV 1.5N/R3.5/3 GE
GTIN (EAN)	4032248065608
Qty.	50 items

**ZQV 1.5N/R3.5/3 GE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	12.15 mm	Depth (inches)	0.4783 inch
Height	9.6 mm	Height (inches)	0.378 inch
Width	2.4 mm	Width (inches)	0.0945 inch
Net weight	0.55 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

**System specifications**

Version For the terminals

**Additional technical data**

Type of fixing	Plugged	Installation advice	Direct mounting
Explosion-tested version	Yes		

**Dimensions**

Pitch in mm (P) 3.50 mm

**General**

Number of poles 3 Installation advice Direct mounting

**Rating data**

Rated voltage 400 V Nominal current 17.5 A

**Important note**

Product information Due to stability and temperature reasons It is only possible to break out 60% of contact elements. The usage of cross connectors reduces the rated voltage to 400 V. The voltage reduced to 25 V if cut cross connection with blank cut edges are used.

**Classifications**

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03

**Technical data**

---

ECLASS 15.0

27-25-03-03

---