


## LM WO 15/70 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

### General ordering data

|            |  |
|------------|--|
| Version    | LaserMark, Conductor and cable markers, 8.2 - 14.3 mm, 15 x 70 mm, white |
| Order No.  | <a href="#">1759871044</a>   |
| Type       | LM WO 15/70 WS   |
| GTIN (EAN) | 403224802695 1   |
| Qty.       | 10 items   |

## LM WO 15/70 WS

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.03 mm | Depth (inches)  | 0.001 inch  |
| Height     | 15 mm   | Height (inches) | 0.5906 inch |
| Width      | 70 mm   | Width (inches)  | 2.7559 inch |
| Net weight | 10.4 g  |                 |             |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General data

|  |  |             |
|--|--|-------------|
| Adhesive                                     | Acrylate                                       |             |
| Material colour according to resistance code | 9  |             |
| Number per sheet                             | 52   |             |
| Type of printing                             | neutral  |             |
| Version                                      | Self-adhesive                                  |             |
| Width  | 70 mm  |             |
| UL 94 flammability rating                    | V-0  |             |
| Operating temperature range, max.            | 150 °C   |             |
| Operating temperature range, min.            | -40 °C   |             |
| Colour                                       | white  |             |
| Halogen                                      | No   |             |
| Basic material                               | Polyester film                                 |             |
| Printed characters                           | without  |             |
| Number of markers per packaging unit         | 520  |             |
| Number of markers per packaging unit         | Form of supply                                 | Label sheet |
|  | Number of combinations per packaging unit      | 10          |
|  | Number of markers per combination              | 52          |
| Size of labelling field                      | 15 x 30 mm                                     |             |
| Number of markers per combination            | 1 Label sheet = 52 Conductor and cable markers |             |
| Operating temperature range                  | -40...150 °C                                   |             |

## Conductor and cable markers

|                                  |                         |                               |                    |
|----------------------------------|-------------------------|-------------------------------|--------------------|
| Halogen                          | No                      | Conductor cross-section, max. | 50 mm <sup>2</sup> |
| Conductor cross-section, min.    | 16 mm <sup>2</sup>      | Conductor O.D., max.          | 14.3 mm            |
| Conductor O.D., min.             | 8.2 mm                  | Text field width              | 14.98 mm           |
| Text field height                | 30 mm                   | Conductor O.D.                | 8.2 - 14.3 mm      |
| Cross-section for connected wire | 16 - 50 mm <sup>2</sup> |                               |                    |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

