


## DEK 5/3,5 MC FSZ 101-110

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |  |
|------------|--|
| Version    | Dekafix, Terminal marker, 5 x 3.5 mm, Pitch in mm (P): 3.50 Weidmueller, white |
| Order No.  | <a href="#">1762320101</a>   |
| Type       | DEK 5/3,5 MC FSZ 101-110   |
| GTIN (EAN) | 403224804365 1   |
| Qty.       | 500 items  |

Technical data

Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 5 mm   | Height (inches) | 0.1968 inch |
| Width      | 3.5 mm | Width (inches)  | 0.1378 inch |
| Net weight | 0.15 g |                 |             |

Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

Environmental Product Compliance

|                          |                             |                  |  |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                  |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |  |
| Product Carbon Footprint | Cradle to gate              | 0.001 kg CO2 eq. |  |

General data

|  |                               |           |  |
|--|-------------------------------|-----------|--|
| Material colour according to resistance code | 9                             |           |  |
| Orientation of print                         | vertical                      |           |  |
| Printing method                              | MC Laser                      |           |  |
| Width  | 3.5 mm                        |           |  |
| UL 94 flammability rating                    | V-2                           |           |  |
| Operating temperature range, max.            | 100 °C                        |           |  |
| Operating temperature range, min.            | -40 °C                        |           |  |
| Colour                                       | white                         |           |  |
| Basic material                               | Polyamide 66                  |           |  |
| Colour of printing                           | black                         |           |  |
| Printed characters                           | Numbers                       |           |  |
| Number of markers per packaging unit         | Form of supply                | MultiCard |  |
| Number of markers per combination            | 1 MultiCard = Terminal marker |           |  |
| Operating temperature range                  | -40...100 °C                  |           |  |
| Application/manufacturer                     | Weidmueller                   |           |  |

Connector markers

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 3.50 mm |
|-----------------|---------|

Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |

**Drawings**

---

---

**Drawing**

---

