

**SM 27/8 K MC NE SI**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	SwitchMark, Device markers, 8 x 27 mm, silver
Order No.	<a href="#">1771930000</a>
Type	SM 27/8 K MC NE SI
GTIN (EAN)	4032248 127085
Qty.	80 items

## SM 27/8 K MC NE SI

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	8 mm	Height (inches)	0.315 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	1.19 g		

## Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.006 kg CO2 eq.

## General data

Adhesive	Double-sided adhesive tape	
Version	Self-adhesive	
Width	27 mm	
UL 94 flammability rating	V-2	
Operating temperature range, max.	60 °C	
Operating temperature range, min.	-40 °C	
Colour	silver	
Halogen	No	
Basic material	Polyamide 66	
Printed characters	without	
Number of markers per packaging unit compatible printer	Form of supply	MultiCard
	<a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a>	
Number of markers per combination	1 MultiCard = Device markers	
Operating temperature range	-40...60 °C	

## Device markers

Halogen	No
---------	----

## Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**Drawings**



## SM 27/8 K MC NE SI

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Complementary products



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	ETO SM 27/8	Version	
Order No.	<a href="#">1720570000</a>	SwitchMark, Protective cap, 8 x 27 mm, Transparent	
GTIN (EAN)	4008190362201		
Qty.	10 ST		