



## LM2NZF 5.08/24/135 3.5SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Product image



Similar to illustration

The high-performance device interface with a high connection density, for standard 2.5mm<sup>2</sup> cross-section wires. Multi-tier PCB terminal in 5.08 mm pitch, with the maintenance-free tension clamp connection in 135° outlet direction.

Rated data:

- 15A / 630V (IEC) or 10A / 300V (UL)
- 0.20 - 2.5mm<sup>2</sup> (IEC) / 26 - 14 AWG (UL)
- Flammability class according to UL 94: V2

Application benefits:

- Simple change of connection method - layout is compatible with multi-tier screw terminals.

### General ordering data

|              |  |
|--------------|--|
| Version      | Printed circuit board terminals, 5.08 mm, Number of poles: 24, 135°, Solder pin length (l): 3.5 mm, orange, Tension-clamp connection, Clamping range, max. : 2.5 mm <sup>2</sup> , Box |
| Order No.    | <a href="#">1764900000</a>   |
| Type         | LM2NZF 5.08/24/135 3.5SN OR BX   |
| GTIN (EAN)   | 4032248103140  |
| Qty.         | 10 items   |
| Product data | IEC: 630 V / 15 A / 0.2 - 2.5 mm <sup>2</sup><br>UL: 300 V / 10 A / AWG 24 - AWG 14  |
| Packaging    | Box  |

## LM2NZF 5.08/24/135 3.5SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|                          |             |                 |             |
|--------------------------|-------------|-----------------|-------------|
| Depth                    | 24.05 mm    | Depth (inches)  | 0.9468 inch |
| Height                   | 29.1 mm     | Height (inches) | 1.1457 inch |
| Height of lowest version | 25.6 mm     | Width           | 61.66 mm    |
| Width (inches)           | 2.4276 inch | Net weight      | 34.2 g      |

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### System parameters

|  |                               |  |                          |
|--|-------------------------------|--|--------------------------|
| Product family                             | OMNIMATE Signal - series LMZF | Wire connection method                       | Tension-clamp connection |
| Mounting onto the PCB                      | THT solder connection         | Conductor outlet direction                   | 135°                     |
| Pitch in mm (P)                            | 5.08 mm                       | Pitch in inches (P)                          | 0.200 "                  |
| Number of poles                            | 24                            | Pin series quantity                          | 2                        |
| Fitted by customer                         | No                            | Number of rows                               | 2                        |
| Solder pin length (l)                      | 3.5 mm                        | Solder pin dimensions                        | 0.7 x 1.0 mm             |
| Solder eyelet hole diameter (D)            | 1.3 mm                        | Solder eyelet hole diameter tolerance (D)+   | 0,1 mm                   |
| Number of solder pins per pole             | 1                             | Screwdriver blade                            | 0.6 x 3.5                |
| Screwdriver blade standard                 | DIN 5264-A                    | Stripping length                             | 7.5 mm                   |
| L1 in mm                                   | 55.88 mm                      | L1 in inches                                 | 2.200 "                  |
| Touch-safe protection acc. to DIN VDE 0470 | IP 20                         | Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch   |
| Protection degree                          | IP20                          | Volume resistance                            | 2.10 mΩ                  |

### Material data

|                                       |          |                                       |          |
|---------------------------------------|----------|---------------------------------------|----------|
| Insulating material                   | PA       | Colour                                | orange   |
| Colour chart (similar)                | RAL 2000 | Insulating material group             | I        |
| Comparative Tracking Index (CTI)      | ≥ 600    | Moisture Level (MSL)                  |          |
| UL 94 flammability rating             | V-0      | Contact material                      | Cu-alloy |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C    |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 100 °C   |
| Temperature range, installation, min. | -25 °C   | Temperature range, installation, max. | 100 °C   |

### Conductors suitable for connection

|  |                           |
|--|---------------------------|
| Clamping range, min.                       | 0.13 mm <sup>2</sup>      |
| Clamping range, max.                       | 2.5 mm <sup>2</sup>       |
| Wire connection cross section AWG, min.    | AWG 24                    |
| Wire connection cross section AWG, max.    | AWG 14                    |
| Solid, min. H05(07) V-U                    | 0.2 mm <sup>2</sup>       |
| Solid, max. H05(07) V-U                    | 2.5 mm <sup>2</sup>       |
| Flexible, min. H05(07) V-K                 | 0.2 mm <sup>2</sup>       |
| Flexible, max. H05(07) V-K                 | 1.5 mm <sup>2</sup>       |
| w. plastic collar ferrule, DIN 46228 pt 4, | 0.25 mm <sup>2</sup> min. |

## LM2NZF 5.08/24/135 3.5SN OR BX

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

w. plastic collar ferrule, DIN 46228 pt 4, 1.5 mm<sup>2</sup>  
max.

w. wire end ferrule, DIN 46228 pt 1, 0.25 mm<sup>2</sup>  
min.

w. wire end ferrule, DIN 46228 pt 1, 1.5 mm<sup>2</sup>  
max.

Plug gauge in accordance with EN 60999 a x b; ø 2.4 mm x 1.5 mm

|                     |  |                              |                        |
|---------------------|--|------------------------------|------------------------|
| Clampable conductor | Cross-section for conductor connection | Type                         | fine-wired             |
|                     |  | nominal                      | 1.5 mm <sup>2</sup>    |
|                     | wire end ferrule                       | Stripping length             | nominal                |
|                     |  | Recommended wire-end ferrule | <a href="#">H1.5/7</a> |

Reference text Length of ferrules is to be chosen depending on the product and the rated voltage., The outside diameter of the plastic collar should not be larger than the pitch (P)

### Rated data acc. to IEC

|   |                        |   |       |
|---|------------------------|---|-------|
| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 15 A  |
| Rated current, max. number of poles (Tu=20°C)                             | 12 A                   | Rated current, min. number of poles (Tu=40°C)                         | 13 A  |
| Rated current, max. number of poles (Tu=40°C)                             | 10 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 630 V |
| Rated voltage for surge voltage class / pollution degree III/2            | 320 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 250 V |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4 kV  |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 4 kV                   |   |       |

### Rated data acc. to CSA

|                                   |        |                                   |        |
|-----------------------------------|--------|-----------------------------------|--------|
| Rated voltage (Use group B / CSA) | 300 V  | Rated voltage (Use group D / CSA) | 300 V  |
| Rated current (Use group B / CSA) | 10 A   | Rated current (Use group D / CSA) | 10 A   |
| Wire cross-section, AWG, min.     | AWG 24 | Wire cross-section, AWG, max.     | AWG 14 |

### Rated data acc. to UL 1059

|                                       |        |                                       |        |
|---------------------------------------|--------|---------------------------------------|--------|
| Rated voltage (Use group B / UL 1059) | 300 V  | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 10 A   | Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 24 | Wire cross-section, AWG, max.         | AWG 14 |

### Packing

|           |           |            |           |
|-----------|-----------|------------|-----------|
| Packaging | Box       | VPE length | 140.00 mm |
| VPE width | 104.00 mm | VPE height | 40.00 mm  |

### Important note

IPC conformity Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

## LM2NZF 5.08/24/135 3.5SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002643    | ETIM 9.0    | EC002643    |
| ETIM 10.0   | EC002643    | ECLASS 14.0 | 27-46-01-01 |
| ECLASS 15.0 | 27-46-01-01 |             |             |


LM2NZF 5.08/24/135 3.5SN OR BX

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

Drawings

Dimensional drawing



Graph

