

VG M50 - MS 68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG MS (standard brass cable gland), Cable glands, straight, M 50, 9 mm, OD min. 22 - OD max. 32 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Brass, nickel-plated
Order No.	1772260000
Type	VG M50 - MS 68
GTIN (EAN)	4032248129911
Qty.	5 items

VG M50 - MS 68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	48 mm	Height (inches)	1.8898 inch
Length	57 mm	Length (inches)	2.2441 inch
Net weight	280.2 g		

Temperatures

Operating temperature -40 °C...100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

Certificate numbers cable gland

Certificate no. cable gland (GERMLLOYD)	E-14047	Certificate no. cable gland (UL)	E-199260
Certificate no. cable gland (cULus)	E-199260	Approval conditions	DNV, UL, cULus

General information

Outer cable diameter, max.	32 mm	Outer cable diameter, min.	22 mm
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Tightening torque	18 Nm
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Halogen	Yes
AF size 1	50 mm	AF size 2	55 mm
AF size	50 mm	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Cable gland	M 50	Basic material	Brass, nickel-plated
Seal insert	NBR	Sealing	NBR
External thread	M 50	Length of thread	9 mm
Torque for cap nut, max.	43.00 Nm	Protection class (UL)	Type 4X
Torque for connecting adapter, max.	18.50 Nm	Torque for connecting adapter, min.	17.50 Nm
Torque for cap nut, min.	41.00 Nm	Clamp insert	Polyamide

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		

VG M50 - MS 68

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M50 MS	Version	
Order No.	1737040000	SKMU MS (brass locknut), Locknut, M 50, 5 mm, Brass, nickel-plated	
GTIN (EAN)	4008190956516		
Qty.	25 ST		

Brass lock nuts, natural finish



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M50 MS SC	Version	
Order No.	0930640006	SKMU MS (brass locknut), Locknut, M 50, 5 mm, Brass	
GTIN (EAN)	4032248976102		
Qty.	5 ST		

Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M50-NP	Version	
Order No.	1736280000	GWDR NP (flat gasket - neoprene), Sealing ring, M 50, Neoprene	
GTIN (EAN)	4008190956073		
Qty.	20 ST		

VG M50 - MS 68

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Polyethylene flat gasket - GWDR PO



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M50-PO	Version	
Order No.	1777980000	GWDR PO (flat gasket - polyethylene), Sealing ring, M 50,	
GTIN (EAN)	4032248158249	Polyethylene	
Qty.	50 ST		

Vulcanised fibre gasket - KSWF



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWF M50	Version	
Order No.	1076720000	KSWF (flat gasket - vulcanised fibre), Sealing ring, M 50, Vulcanized	
GTIN (EAN)	4032248838646	fibre	
Qty.	25 ST		

Nylon flat gasket - KSWN



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWN M50	Version	
Order No.	0900660000	KSWN (flat gasket - nylon), Sealing ring, M 50, Nylon 6	
GTIN (EAN)	4032248850105		
Qty.	25 ST		