

**SAI-SA-4-IDC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems. The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

**General ordering data**

|            |                                 |
|------------|---------------------------------|
| Version    | Field attachable connector, M12 |
| Order No.  | <a href="#">1766810000</a>      |
| Type       | SAI-SA-4-IDC                    |
| GTIN (EAN) | 4032248148233                   |
| Qty.       | 1 items                         |

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 13.3 g |
|------------|--------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Technical data customisable plug-in connectors

|                               |                     |                               |                                    |
|-------------------------------|---------------------|-------------------------------|------------------------------------|
| Number of poles               | 4                   | Coding                        | none                               |
| Contact surface               | tinned              | Type of connection            | Insulation displacement connection |
| Housing main material         | CuZn                | Insulation resistance         | 108 Ω                              |
| Cable diameter, max.          | 5.1 mm              | Cable diameter, min.          | 4 mm                               |
| Conductor cross-section, max. | 0.5 mm <sup>2</sup> | Conductor cross-section, min. | 0.25 mm <sup>2</sup>               |
| Nominal voltage               | 32 V                | Nominal current               | 4 A                                |
| Protection degree             | IP67                | Plugging cycles               | ≥ 50                               |
| Pollution severity            | 3                   | Gender of contact             | Male                               |
| Shield connection             | No                  | Threaded ring material        | Diecast zinc                       |
| Temperature range of housing  | -25...+85 °C        |                               |                                    |

### General Info

|                       |        |                        |                     |
|-----------------------|--------|------------------------|---------------------|
| Number of poles       | 4      | Connection 1           | M12                 |
| Connection 2          | IDC    | Description of article | SAIS IDC / SAIB IDC |
| Housing main material | CuZn   | Connection thread      | M12                 |
| Contact surface       | tinned | Protection degree      | IP67                |
| Plugging cycles       | ≥ 50   |                        |                     |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002635    | ETIM 9.0    | EC002635    |
| ETIM 10.0   | EC002635    | ECLASS 14.0 | 27-44-01-16 |
| ECLASS 15.0 | 27-44-01-16 |             |             |