### **DEK 5/3.5 MC SDR**



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com









Similar to illustration

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### **General ordering data**

Version	Dekafix, Terminal marker, 5 x 3.5 mm, Pitch in mm
	(P): 3.50 Weidmueller, To customer specification
Order No.	1767730000
Туре	DEK 5/3.5 MC SDR
GTIN (EAN)	4032248102532
Qty.	100 items

Catalogue status / Drawings



## **DEK 5/3.5 MC SDR**



Weidmüller Interface GmbH & Co. KG

2

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

**Approvals** 

Approvais				
ROHS	Conform			
Dimensions and weights				
				_
Height	5 mm	Height (inches)		0.1968 inch
Width	3.5 mm	Width (inches)		0.1378 inch
Net weight	0.04 g			
Temperatures				
Operating temperature range	-40100 °C			
Environmental Product Comp	liance			
	<u> </u>			
RoHS Compliance Status	Compliant without exemptio	n		
REACH SVHC	No SVHC above 0.1 wt%			
Product Carbon Footprint	Cradle to gate		0.002 kg CO2 eq.	
General data				
Material colour according to resistance code	9			
Orientation of print	horizontal and vertical			
Printing method	MC Laser			
Width	3.5 mm			
UL 94 flammability rating	V-2			
Operating temperature range, max.	100 °C			
Operating temperature range, min.	-40 °C			
Colour	To customer specification			·
Basic material	Polyamide 66			
Colour of printing	black			
Printed characters	Requires M-Print PRO File			
Number of markers per packaging unit	Form of supply		MultiCard	
Number of markers per combination	1 MultiCard = Terminal mark	er		
	40 40000			

# Application/manufacturer Connector markers

Operating temperature range

Pitch in mm (P)	3.50 mm	

-40...100 °C

Weidmueller

#### Classifications

EC000761	ETIM 7.0	EC000761
EC000761	ETIM 9.0	EC000761
EC000761	ECLASS 9.0	27-14-11-37
27-14-11-37	ECLASS 10.0	27-14-11-37
27-28-11-01	ECLASS 12.0	27-28-11-01
27-28-11-01	ECLASS 14.0	27-28-11-01
27-28-11-01		
	EC000761 EC000761 27-14-11-37 27-28-11-01 27-28-11-01	EC000761 ETIM 9.0 EC000761 ECLASS 9.0 27-14-11-37 ECLASS 10.0 27-28-11-01 ECLASS 12.0 27-28-11-01 ECLASS 14.0

Creation date 02.12.2025 09:47:04 MEZ

Catalogue status / Drawings

# **Data sheet**

## **DEK 5/3.5 MC SDR**



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Drawings

### **Drawing**

