

**VP M16-MS65**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**



For sealing surplus threaded holes to maintain the IP class of protection

**General ordering data**

Version	VPMS (blanking plug in brass), Blanking plug, in closed state, M 16, 5 mm, Brass, nickel-plated
Order No.	<a href="#">1777730000</a>
Type	VP M16-MS65
GTIN (EAN)	4032248158003
Qty.	100 items

**VP M16-MS65**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Height	8 mm	Height (inches)	0.315 inch
Length	8 mm	Length (inches)	0.315 inch
Diameter	18 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	4 mm	Net weight	4.4 g

**Temperatures**

Operating temperature -40 °C... 100 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203

**Technical properties**

Protection degree IP68 - 5 bar (30 min.)

**General information**

Head diameter	18.00 mm	O-Ring	NBR
Silicone	No	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	No	Protection degree	IP68 - 5 bar (30 min.)
Cable gland	metric	Basic material	Brass, nickel-plated
Diameter of sealing ring	16.00 mm	Sealing	NBR
External thread	M 16	Length of thread	5 mm

**Technical data**

Colour silver Protection degree IP68 - 5 bar (30 min.)

**Technical data**

Protection degree IP68 - 5 bar (30 min.)

**Classifications**

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

