

VP M50-MS65**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPMS (blanking plug in brass), Blanking plug, in closed state, M 50, 9 mm, Brass, nickel-plated
Order No.	177780000
Type	VP M50-MS65
GTIN (EAN)	4032248158058
Qty.	25 items

VP M50-MS65

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	15 mm	Height (inches)	0.5906 inch
Length	15 mm	Length (inches)	0.5906 inch
Diameter	54 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	8 mm	Net weight	69.84 g

Temperatures

Operating temperature -40 °C... 100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203

General information

Head diameter	54.00 mm	O-Ring	NBR
Silicone	No	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	No	Protection degree	IP68 - 5 bar (30 min.)
Cable gland	metric	Basic material	Brass, nickel-plated
Diameter of sealing ring	50.00 mm	Sealing	NBR
External thread	M 50	Length of thread	9 mm

Classifications

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

