

VP M63-MS65**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPMS (blanking plug in brass), Blanking plug, in closed state, M 63, 10 mm, Brass, nickel-plated
Order No.	1777790000
Type	VP M63-MS65
GTIN (EAN)	4032248158065
Qty.	10 items

VP M63-MS65

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	16 mm	Height (inches)	0.6299 inch
Length	16 mm	Length (inches)	0.6299 inch
Diameter	67 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	9 mm	Net weight	99.97 g

Temperatures

Operating temperature -40 °C... 100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203

General information

Head diameter	67.00 mm	O-Ring	NBR
Silicone	No	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	No	Protection degree	IP68 - 5 bar (30 min.)
Cable gland	metric	Basic material	Brass, nickel-plated
Diameter of sealing ring	63.00 mm	Sealing	NBR
External thread	M 63	Length of thread	10 mm

Classifications

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

