

ZPE 4-2/2AN**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

General ordering data

| | |
|------------|--|
| Version | Z-series, PE terminal, Rated cross-section: 4 mm ² , Tension-clamp connection, Green/yellow |
| Order No. | 1770380000 |
| Type | ZPE 4-2/2AN |
| GTIN (EAN) | 4032248142972 |
| Qty. | 50 items |

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E60693 |

Dimensions and weights

| | | | |
|--------------------------|-------------|----------------|-------------|
| Depth | 45.5 mm | Depth (inches) | 1.7913 inch |
| Depth including DIN rail | 46 mm | Height | 61.5 mm |
| Height (inches) | 2.4213 inch | Width | 6.1 mm |
| Width (inches) | 0.2402 inch | Net weight | 14.47 g |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -50 °C...75 °C |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|---------------------------|-------|--------|--------------|
| Basic material | Wemid | Colour | Green/yellow |
| UL 94 flammability rating | V-0 | | |

Rating data IECEx/ATEX

| | | | |
|--------------------------------|-------------------|---------------------------------|-------------------|
| Certificate No. (ATEX) | DEMKO16ATEX1808U | Certificate No. (IECEx) | IECExULD16.0036U |
| Wire cross section max. (ATEX) | 6 mm ² | Wire cross section max. (IECEx) | 6 mm ² |
| Marking EN 60079-7 | Ex eb II C Gb | Ex 2014/34/EU label | II 2 G D |

System specifications

| | | | |
|-------------------------------------|---|-----------------------------------|-------|
| Version | Tension-clamp connection, With PE connection, One end without connector | End cover plate required | Yes |
| Number of potentials | 1 | Number of levels | 1 |
| Number of clamping points per level | 2 | Levels cross-connected internally | No |
| PE connection | Yes | Mounting rail | TS 35 |
| PE function | Yes | PEN function | No |

Additional technical data

| | | | |
|--------------------------|-------|-----------------------------|---------|
| Open sides | right | Number of similar terminals | 1 |
| Explosion-tested version | Yes | Type of mounting | Snap-on |

ZPE 4-2/2AN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

CSA rating data

| | | | |
|-------------------------------|--------|-----------------------|----------------|
| Wire cross section max. (CSA) | 10 AWG | Certificate No. (CSA) | 200039-1152892 |
| Wire cross section min. (CSA) | 26 AWG | | |

Conductors for clamping (additional connection)

Connection type, additional connection Tension-clamp connection

Conductors for clamping (rated connection)

| | | | |
|---|--|-------------|----------------------|
| Gauge to IEC 60947-1 | A3 | | |
| Wire connection cross section AWG, max. | AWG 10 | | |
| Connection direction | Inclined / angled | | |
| Stripping length | 10 mm | | |
| Type of connection | Tension-clamp connection | | |
| Number of connections | 2 | | |
| Clamping range, max. | 6 mm ² | | |
| Clamping range, min. | 0.13 mm ² | | |
| Blade size | 0.6 x 3.5 mm | | |
| Wire connection cross section AWG, min. | AWG 26 | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 4 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.13 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.13 mm ² | | |
| Wire connection cross section, finely stranded, max. | 4 mm ² | | |
| Wire connection cross section, finely stranded, min. | 0.13 mm ² | | |
| Connection cross-section, stranded, max. | 4 mm ² | | |
| Connection cross-section, stranded, min. | 0.13 mm ² | | |
| Wire connection cross-section, solid core, max. | 6 mm ² | | |
| Wire connection cross-section, solid core, min. | 0.13 mm ² | | |
| Connection cross-section, finely stranded, min. | 0.13 mm ² | | |
| Tube length for wire-end ferrule with plastic collar DIN 46228/4 | Tube length | min. | 8 mm |
| | | max. | 10 mm |
| | Cross-section for conductor connection | nominal | 0.5 mm ² |
| | | Tube length | min. |
| | max. | | 12 mm |
| | Cross-section for conductor connection | nominal | 0.75 mm ² |
| | | Tube length | min. |
| | max. | | 12 mm |
| | Cross-section for conductor connection | nominal | 1 mm ² |
| | | Tube length | min. |
| | max. | | 12 mm |
| | Cross-section for conductor connection | nominal | 1.5 mm ² |

ZPE 4-2/2AN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | | |
|---|--|----------------------|----------------------|
| | Tube length | min. | 8 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | nominal | 2.5 mm ² |
| | | | |
| Tube length for twin wire-end ferrule | Tube length | min. | 10 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | nominal | 4 mm ² |
| | | | |
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Tube length | min. | 8 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | nominal | 0.5 mm ² |
| | | | |
| | Tube length | min. | 8 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | nominal | 0.75 mm ² |
| | | | |
| | Tube length | nominal | 10 mm |
| | | | |
| | Cross-section for conductor connection | nominal | 0.5 mm ² |
| | | | |
| Tube length | nominal | 10 mm | |
| | | | |
| Cross-section for conductor connection | nominal | 0.75 mm ² | |
| | | | |
| Tube length | nominal | 10 mm | |
| | | | |
| Cross-section for conductor connection | nominal | 1 mm ² | |
| | | | |
| Tube length | min. | 10 mm | |
| | max. | 12 mm | |
| Cross-section for conductor connection | nominal | 1.5 mm ² | |
| | | | |
| Tube length | min. | 10 mm | |
| | max. | 12 mm | |
| Cross-section for conductor connection | nominal | 2.5 mm ² | |
| | | | |
| Tube length | nominal | 12 mm | |
| | | | |
| Cross-section for conductor connection | nominal | 4 mm ² | |
| | | | |

General

| | | | |
|---|---------------|---|--------|
| Wire connection cross section AWG, max. | AWG 10 | Wire connection cross section AWG, min. | AWG 26 |
| Standards | IEC 60947-7-2 | Mounting rail | TS 35 |

Rating data

| | | | |
|--|-------------------|--|---------------|
| Rated cross-section | 4 mm ² | Rated voltage to adjoining terminal | 800 V |
| Rated DC voltage | 800 V | Standards | IEC 60947-7-2 |
| Volume resistance according to IEC 60947-7-x | 1 mΩ | Rated impulse withstand voltage to adjacent terminal | 8 kV |
| Power loss in accordance with IEC 60947-7-x | 1.02 W | Pollution severity | 3 |

UL rating data

| | | | |
|---|--------|---|--------|
| Conductor size Factory wiring max. (UR) | 10 AWG | Conductor size Factory wiring min. (UR) | 26 AWG |
| Certificate No. (UR) | E60693 | Conductor size Field wiring min. (UR) | 26 AWG |
| Conductor size Field wiring max. (UR) | 10 AWG | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000901 | ETIM 9.0 | EC000901 |
| ETIM 10.0 | EC000901 | ECLASS 14.0 | 27-25-01-03 |
| ECLASS 15.0 | 27-25-01-03 | | |

Drawings

