

WTW WF10/WF12 2300**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

General ordering data

Version	Bolt-type screw terminals, Partition plate, grey, 2 mm
Order No.	1780920000
Type	WTW WF10/WF12 2300
GTIN (EAN)	4032248241149
Qty.	20 items

WTW WF10/WF12 2300

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	76.45 mm	Depth (inches)	3.0098 inch
Height	155.8 mm	Height (inches)	6.1338 inch
Width	2 mm	Width (inches)	0.0787 inch
Mounting dimension - width	2 mm	Net weight	41.05 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	160 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Epoxy resin	Colour	grey
UL 94 flammability rating	V-0		

System specifications

Version	End and intermediate plate
---------	----------------------------

Additional technical data

Snap-on	No	Installation advice	Direct mounting
---------	----	---------------------	-----------------

General

Installation advice	Direct mounting	Operating temperature range, max.	160 °C
---------------------	-----------------	-----------------------------------	--------

Classifications

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		